



# VRoHS (€

#### **FEATURES**

- Interchangeable
- Low Noise
- Robust: High Over-Range Capability
- High Reliability
- Low Deflection
- Low Off Center Errors
- Fast Response Time
- Long Cycle Life Expectancy

#### **APPLICATIONS**

- Batch Weighing
- Robotics End-Effectors
- Variable Force Control
- Load and Compression Sensing
- Assembly Line Force Measurement
- Pumps
- Hoist and Winch Loads
- Weighing

# FC23

# Compression Load Cell

#### **SPECIFICATIONS**

- 50 2000 lbf Ranges
- High Level or mV
- Interchangeable
- Compact Load Button Design
- Industry Standard Packaging
- CE Compliance

The **FC23** is a high compression force sensor that creates new markets previously unrealizable due to cost and performance constraints. The FC23 offers normalized zero and span for interchangeability and is thermally compensated for changes in zero and span with respect to temperature.

The FC23 incorporates MEAS' proprietary Microfused™ technology which employs micromachined silicon piezoresistive strain gages fused with high temperature glass to a high performance stainless steel substrate. Microfused™ technology eliminates agesensitive organic epoxies used in traditional load cell designs providing excellent long-term span and zero stability. The FC23 measures direct force and is therefore not subject to lead-die fatigue failure common with competitive designs which use a pressure capsule embedded within a silicone gel-filled cavity. Operating at very low strains, Microfused™ technology provides an essentially unlimited cycle life expectancy, superior resolution, and high over-range capabilities.

The FC23 brings your OEM product to life whether you need thousands or millions of load cells annually. Although the standard model is ideal for a wide range of applications, our dedicated design team at our Load Cell Engineering Center is ready to provide you with custom designs for your OEM applications.

Please refer to models FS20 and FC22 for lower force applications.

# STANDARD RANGES

Range	lbf
0 to 0050	•
0 to 0100	•
0 to 0250	•
0 to 0500	•
0 to 1000	•
0 to 2000	•

# PERFORMANCE SPECIFICATIONS

Unless otherwise specified: Supply Voltage: 5.0V, Ambient Temperature: 25°C

MIN	TYP	MAX	UNITS	NOTES
95	100	105	mV	1
95	100	105	mV	1
3.8	4.0	4.2	V	1
-50	0	50	mV	1
-20	0	20	mV	1
0.3	0.5	0.7	V	1
-1		1	%Span	2
	3		kΩ	
	2.2		kΩ	
	2.2		kΩ	
-2.5	±1	2.5	%Span	3
-2.5	±1	2.5	%Span	3
2	3.3	6.7	V	1
2	5	10	V	1
4.5	5	5.5	V	1
	1.0		ms	
	±1		%Span	
		2.5X	Rated	
0		50	°C	
-40		+85	°C	
-40		+85	°C	
50			МΩ	
		0.05	mm	
0		0.05 90	mm %RH	
	MIN  95  95  3.8  -50  -20  0.3  -1  -2.5  -2.5  2  4.5	95 100 95 100 3.8 4.0 -50 0 -20 0 0.3 0.5 -1 3 2.2 2.2 -2.5 ±1 -2.5 ±1 2 3.3 2 5 4.5 5 1.0 ±1	MIN         TYP         MAX           95         100         105           95         100         105           3.8         4.0         4.2           -50         0         50           -20         0         20           0.3         0.5         0.7           -1         1         1           3         2.2         2.2           2.2         2.2         2.5           2.5         ±1         2.5           2         5         10           4.5         5         5.5           1.0         ±1           2.5X         0         50           -40         +85           -40         +85           50	MIN         TYP         MAX         UNITS           95         100         105         mV           95         100         105         mV           3.8         4.0         4.2         V           -50         0         50         mV           -20         0         20         mV           -20         0         20         mV           0.3         0.5         0.7         V           -1         1         %Span           3         kΩ         kΩ           2.2         kΩ         kΩ           2.2.2         kΩ         xΩ           2.5         ±1         2.5         %Span           2         3.3         6.7         V           2         5         10         V           4.5         5         5.5         V           1.0         ms         ±1         %Span           2.5X         Rated         °C           -40         +85         °C           -40         +85         °C           50         MΩ

#### For custom configurations, consult factory.

#### Notes


- 1. Ratiometric to supply.
- Best fit straight line.
- 3. Maximum temperature error over compensated range with respect to 25°C.


# **CE Compliance**


IEC61000-4-2: [4kV/ 4 kV (Air/Contact)]

IEC61000-4-3: (3 V/m)

# **DIMENSIONS**








### CONNECTIONS

FC2301:
MILLIVOLT OUTPUT VERSION




FC2311:


MILLIVOLT OUTPUT VERSION

MODULE

RED V+




FC2331: AMPLIFIED OUTPUT VERSION




### WIRE NOTE:

P/N	WIRE CONNECTIONS
FC2301 FC2311	4 CORE WIRE (AWG32 OR AWG34, 125°C, 300V YELLOW: +OUTPUT BLUE: -OUTPUT RED: V+ GREEN: GND
FC2331	3 CORE WIRE (AWG32 OR AWG34, 125°C, 300V RED: V+ YELLOW: +OUTPUT BLACK: GND



### **ORDERING INFORMATION**



#### **NORTH AMERICA**

Measurement Specialties, Inc., a TE Connectivity company 45738 Northport Loop West Fremont, CA 94538 Tel: +1 800 767 1888

Fax: +1 510 498 1578

customercare.frmt@te.com

# TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

# **EUROPE**

MEAS France SAS, a TE Connectivity company 26 Rue des Dames 78340 Les Clayes-sous-Bois, France Tel: +33 (0) 130 79 33 00 Fax: +33 (0) 134 81 03 59

customercare.lcsb@te.com

#### **ASIA**

Measurement Specialties (China) Ltd., a TE Connectivity company No. 26 Langshan Road Shenzhen High-Tech Park (North) Nanshan District, Shenzhen, 518057 China

Tel: +86 755 3330 5088 Fax: +86 755 3330 5099 customercare.shzn@te.com

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.