

Datasheet

**RS Pro Multi Function 16 Time Delay Relay, Screw, 0.1 s
→ 120 Days, SPDT, 1 Contacts, DPDT, 24 → 240 V ac/dc**
RS Stock No: **896-6841**



Product Details

RS Pro multi function 16 time delay relay has highly comprehensive features that include 16 different timing functions. The time delay relay includes supply voltage start and signal start options. It comes with a terminal screw and has a time range of 0.1 s to 120 days. It has SPDT, DPDT switch and contact configuration with 1 contact and supply voltage of 24 to 240 V ac/dc.

Features and Benefits

- 16 timing functions selected by dip switch
- 22.5 mm width
- DIN rail mounting
- Multi function with signal start and supply start
- 2 independent relay outputs with either both relays times or one timed and one instantaneous
- Wide input signal and supply range 24 to 240 V ac/dc
- 0.1 s - 120 days timing range
- High timing accuracy
- LED indicators for power supply and relay status
- IP20 (terminals), IP40 (enclosure) protection

Specifications:

Contact Material	Silver Nickel
Number of Timer Functions	16
Power Supply	External
Switch Configuration	DPDT
Time Increment	Seconds
Depth	100.5 mm
Length	83 mm
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-10°C
Number of Contacts	1
Width	22.5 mm
Contact Configuration	CO
Current Maximum	5 A
Maximum Voltage	240 V ac/dc
Minimum Voltage	24 V ac/dc
Mode of Operation	Multi Function
Mounting Type	DIN Rail
Supply Voltage	24 to 240 V ac/dc
Terminal Type	Screw
Time Delay	200 ms
Time Range	0.1 s to 120 days
IP Rating	IP20, IP40