

Shrink sleeve - WMS 12,7 (EX20)R BK - 0800422

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Shrink sleeve, Roll, black, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK W: without print, unperforated, mounting type: slide on, cable diameter range: 4.2 - 12.7 mm, lettering field size: 20 x 20000 mm

Why buy this product

- Available in the form of continuous rolls and can be printed on both sides using the THERMOMARK W2 printer
- The shrink sleeves are automatically perforated or cut to the required length during the printing process
- UL 224 (125°C, 600 V, all tubing)
- MIL-STD-202G, SAE AMS-DTL-23053, SAE AS-81531
- CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)
- Individual markers can be cut to any length up to 1 m



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 626200
GTIN	4046356626200

Technical data

Dimensions

Length (b)	20 m
Width (a)	20 mm
Cable diameter	4.2 mm ... 12.7 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

General

Color	black
Base element material	polyolefine
Type	Shrink sleeve
Components	halogen-free

Shrink sleeve - WMS 12,7 (EX20)R BK - 0800422

Technical data

General

Material	Polyolefine
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	without print
Number of individual labels	660
Number of individual labels per row	1
Marking mounting type	slide on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Approvals

Approvals

Approvals

CSA / UL Recognized

Ex Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	252259
-----	---	---	--------

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 310982
---------------	---	---	---------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>