

## Media module - FL SFP FX - 2891081

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



The small form-factor plug-in module provides a fiber optic interface with a data transmission speed of 100 Mbps with a wavelength of 1310 nm (long).


### Why buy this product

- Network structure according to IEC 61850
- IEEE 1613



**IEC 61850-3**

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 800952
GTIN	4046356800952

### Technical data

#### Dimensions

Width	13.7 mm
Height	8.95 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (non-condensing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C (non-condensing)
Permissible humidity (operation)	30 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	30 % ... 95 % (non-condensing)
Air pressure (operation)	86 kPa ... 108 kPa (1500 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)

#### Interfaces

Interface 2	Ethernet FO
No. of ports	1 (LC multi-mode)
Transmission physics	multi-mode fiberglass

# Media module - FL SFP FX - 2891081

## Technical data

### Interfaces

Transmission speed	100 Mbps
Transmission length	typ. 2 km
Wavelength	1310 nm
Signal LEDs	depending on the Factoryline device

### Function

Basic functions	SFP module as FO port
Status and diagnostic indicators	via a Factoryline device

### Supply voltage

Supply voltage	3.3 V (via Factoryline switch)
----------------	--------------------------------

### General

Mounting type	Insert in SFP slot
Type AX	Factoryline devices with SFP slot
Net weight	30.7 g
Housing material	Metal

### Standards and Regulations

Vibration (storage/transport)	5g, 150 Hz, in acc. with IEC 60068-2-6
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 10;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Approvals


### Approvals

#### Approvals

EAC / RINA / DNV GL / LR / BSH



#### Ex Approvals

### Approval details

EAC		RU *- DE.A*30.B.01735
-----	-------------------------------------------------------------------------------------	--------------------------

## Media module - FL SFP FX - 2891081

### Approvals

RINA		<a href="http://www.rina.org/en">http://www.rina.org/en</a>	ELE205816XG
DNV GL		<a href="http://exchange.dnv.com/tari/">http://exchange.dnv.com/tari/</a>	TAA00000YV
LR		<a href="http://www.lr.org/en">http://www.lr.org/en</a>	17/20056
BSH		<a href="http://www.bsh.de/de/index.jsp">http://www.bsh.de/de/index.jsp</a>	Nr. 966

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>