



Actual



Family

**Catalog Number:** CC-NPT-1-B  
**Product ID:** 7TAD105060R0003  
**UPC Number:** 78621095586  
**Status:** Active

Cable Gland with NPT Threads, NPT Thread Size 1 Inch, Cord Range 0.709 Inch/18mm to 0.984 Inch/25mm, Thread Length 0.709 Inch/18mm, IP68 Rating, Halogen Free, Nylon, Black

- Sturdy cable sealing mechanism which results in superior strain relief.
- Compact size ensures quick and easy installation in cramped spaces
- Non-metallic construction provides excellent corrosion, chemical and impact resistance.

### Header

3D Model Available on Website

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Cable Glands
Special Features	Sturdy Cable Sealing Mechanism Which Results In Superior Strain Relief
Application	Ideal for Connections and Strain Relief in Cramped Spaces
Standard	UL E13938, CSA
Size	1 Inch
Conductor Range	0.709 Inch/18mm to 0.984 Inch/25mm
Material	Nylon
Color	Black
NEMA Rating	NEMA 4
Temperature Rating	-30 to +80 Degrees C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 inch
Thread length	18.0mm
Suitable for cable diameter	18.0-25.0mm
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP68
Colour	Black
Model	Straight
Operating temperature	-30-+80°C

### Packaging

Inner Quantity	20
Outer Quantity	100
Outer Dimensions (inches)	23.6x7x10.5
Weight Uom	0.09 lbs. Each

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000004
Instruction Sheet 1	ta02021-tb2

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)