



Part Number: 73607W

MachFlex™ Moderate 600V Control, (7) 16 AWG (26x30) BC, PVC/PVC, AWM, CE

[Request Sample](#)

Product Description

Six 16 AWG stranded (26x30) bare copper conductors plus ground wire, lubricated PVC insulation, oil-resistant PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Conductors
Conductor	16	26x30	BC - Bare Copper	6
Ground	16	26x30	BC - Bare Copper	1

Conductor Count:	7
Total Number of Pairs:	N/A
Conductor Size:	16 AWG

Insulation

Element	Material	Nominal Diameter	Nominal Wall Thickness
Conductor	PVC - Polyvinyl Chloride	0.104 in	0.022 in
Ground	PVC - Polyvinyl Chloride		

Color Chart

Color
Black and Numbered

Outer Shield Material

Type	Material
Unshielded	Unshielded

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.390 in	0.035 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
4.1 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	
34 pF/ft	
Shielding:	Unshielded

Inductance

Nominal Inductance
.180 µH/ft

Voltage

UL Voltage Rating

600 V

Temperature Range

UL Temp Rating:	90°C
Operating Temp Range:	-40°C To 90°C (Static), -5°C To 90°C (Flexing)

Mechanical Characteristics

Oil Resistance:	Yes
Flex Cycle Rating:	1 Million Cycles
Bulk Cable Weight:	216 lbs/1000ft
Max Recommended Pulling Tension:	143 lbs
Min Bend Radius (Continuous Flexing):	2.0 in
Min Bend Radius/Minor Axis:	2.0 in

Standards

UL AWM Style:	AWM 2587
CSA AWM Specification:	AWM I/II A/B
Other Specification:	VDE 0472, Section 803 Oil Test

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes

Flammability, LSOH, Toxicity Testing

CSA Flammability:	FT1
UL voltage rating:	600 V RMS

Part Number

Variants

Item #	Color
73607W 008100	Gray
73607W 0081000	Gray
73607W 008500	Gray

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.