



ENGLISH

Datasheet Foot switch, 2-pedal,unguarded



RS Article No.1253713

Specifications:

Operating Frequency: 60 ops/min

Insulation Resistance: $>100M\Omega@500V$ DC

Contact Resistance: $<25m\Omega$ (initial) Rated Thermal Current: 10A/600VAC

Electrical Rating: AC 15 A600 (IEC947-5-1) DC 13 Q300

Dielectric Strength: 1000VAC for 1 min between current carrying parts

2500VAC for 1 min between non-current carrying parts

Service Life: Mechanically 1X10 ⁶ Electrically 5X10⁵

Operating Temperature: $-30\sim +80$ °C (-22 ~ 176 °F)

Humidity: <95%RH

Degree of Protection: IP65

Size (LXWXH): 220X192X62mm

10/05/2016

Features:

- Robust aluminum alloy die cast body
- High current carrying capacity
- Galvanically separated contacts
- Screw terminals with self-lifting clamps for easy wiring
- Positive opening of NC contacts
- UL/CSA APPROVAL(E216958)
- Snap action with dual pedal
- Threaded hole available:M20*1.5





