

## Datasheet

### Foot switch, Heavy-duty industrial model




RS Article No.1253714

#### Specifications:

Operating Frequency:	60 ops/min
Insulation Resistance:	>100MΩ@500V DC
Contact Resistance:	<25mΩ (initial)
Rated Current/Voltage:	20A 125VAC/250VAC/480VAC 1.5HP/125VAC,2HP/250VA
Dielectric Strength:	1000VAC for 1 min between current carrying parts 2500VAC for 1 min between non-current carrying parts
Service Life:	Mechanically 1X10 <sup>6</sup> Electrically 5X10 <sup>5</sup>
Operating Temperature:	-20~+80°C (-4~176°F)
Degree of Protection:	IP65
Size (LXWXH):	228X157X140mm

#### Features:

- Treadle and housing constructed from cast iron for strength and durability
- Strong cast aluminium guard construction
- Anti-skid rubber feet and three holes for rigid mounting to floor or equipment
- UL/CSA/CE/CCC Certified
- SPDT TYPE
- Momentary type
- M20 Conduit type



#### Wiring Diagram

