

# Straight Blade Devices

## 20A, 3 Phase 250V AC, 3 Pole, 4 Wire Grounding

### Single Receptacle

# HUBBELL

### Features

- Industrial Heavy Duty Receptacle
- Deep body design
- Impact resistant

### Ordering Information

Description	Device Color	UPC	Catalog Number
Receptacle, black	Black	783585015880	HBL8420

### Listings

UL Listed to UL498 File E1706  
 CSA Certified to C22.2 No. 42 File 280C  
 NEMA® WD-6 Compliant

### Specifications

Body	Nylon
Base	PBT
Contacts	Brass
Mounting Plate	Steel
Terminal Screws	Brass
Terminal Clamp	Nickel plated steel
Mounting Screws	Plated steel
Ground Contact Assembly	Brass

### Performance

#### Electrical



Current Interrupting Certified for current interrupting at full rated current  
 Dielectric Voltage Withstands 2,000V minimum

#### Mechanical

Terminal Accommodation #14-#10 AWG copper stranded or solid conductor only  
 Terminal Identification Terminals identified in accordance with UL 498 and CSA

#### Environmental

Flammability UL 94 V-2  
 IP Suitability IP20  
 Operating Temperatures Maximum continuous 75°C, minimum -40°C (w/o impact)



### Online Resources

Customer Use Drawing  
 eCatalog  
 Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

