Contractor Series LED RT5/6 Recessed Downlight Kit



- Reduces energy consumption

- Lasts up to 5.5 times longer than

- No warm-up time, instant-on with

full light output and stable lamp to

up to 86%

lamp color

- 120V input voltage

incandescent lamps

11,000 Hour Life



The Contractor Series RT5/6 is a 5" and 6" compatible LED recessed downlight kit creating high performing white light and is optimized for new construction and retrofit applications. Installation is done quickly and easily in most standard 5" or 6" Insulated Ceiling (IC) housings, Airtight (AT) housings and non-IC housings.

Dimming

The Contractor Series LED RT5/6 recessed downlight kits are dimmable to 10% with standard 120V electronic low voltage dimmers (recommended), incandescent or magnetic low voltage dimmers. In some cases, standard incandescent dimmers require a minimum load of typically >40 watts on the circuit for full range dimming performance (four LED modules). For dimming with digital (smart) multi-location dimmers or when dimming fewer than four LED modules, electronic low-voltage (ELV) dimmers are required (some ELV dimmers need a neutral connection in the wallbox).

Application Information

Applications

- Healthcare
- Hospitality
- Office
- Property Management
- Residential
- Retail

Key Features & Benefits

- Lumen package:
 - 625 lumens
- Replacement for 65W incandescent lamps
- RT5/6 fits into most 5" and 6" recessed downlight fixtures
- CCT: 2700K/3000K/4000K/5000K
- CRI: 80
- Beam angle: 80°
- Dimmable down to 10%
- 11,000 hour life (L₇₀)
- Suitable for dry, damp and wet locations

Quality of Light

The Contractor Series LED RT provides good color rendering (80), and a selection of color temperatures (2700K, 3000K, 4000K and 5000K). LEDs have virtually no UV or infrared radiation to damage or fade furnishings, art or other objects.

Optical Design

Optical design efficiently directs light output in an 80° beam angle with low glare.

Accessories

Assorted color retrofit trims, retrofit band.

Product Offering

Lumen				
Output	Wattage	Color Temperature	CRI	
625	9	2700K, 3000K, 4000K, 5000K	80+	

Specifications and Certifications











Specification Data

Catalog #	Туре
Project	
Project Comments	
Prepared by	

Specifications

Energy Data

Minimum Starting Temp: -40°F (-40°C) EMI/RFI: FCC Title 47 CFR, Part 15, Class B Sound Rating: <24dBA Input Voltage: 120V Power Factor: >0.90 Input Frequency: 60Hz

THD: <20%	
Input Power: 9W	
Input Current: 0.08A & 0.1A	
Maximum Ambient Operating Temperature	
(Insulated Ceiling or Non-Insulated Ceiling): (40°C)	104°F

Lighting Data Lumen Output: 625 Color Correlated Color Temperature (CCT): 2700K, 3000K, 4000K, 5000K Color Rendering Index (CRI): 80

Ordering Information

ltem Number	Ordering Abbreviation	Recessed Housing	Replaced Incandescent Wattage	Nominal Wattage (W)	Delivered Light Output (Im)	Color Temperature	CRI	R9	Avg. Rated Life (hrs)*
74404	LED/RT5/6/625/827	5 in and 6 in	65W	9	625	2700K	80		11,000
74405	LED/RT5/6/625/830	5 in and 6 in	65W	9	625	3000K	80		11,000
74406	LED/RT5/6/625/840	5 in and 6 in	65W	9	625	4000K	80		11,000
74407	LED/RT5/6/625/850	5 in and 6 in	65W	9	625	5000K	80		11,000

* LED lamp life is defined as the number of hours when 50% of an average group of identical lamps reached 70% of its initial lumens.

Orderin	ng Guide	•					
LED	1	RT5/6	1	625	1	8	30
LED		Product Name:		Light Output		CRI >80	Color Temperature
		5/6=fits 5" and 6" housing		625 lm			3000K

Energy Savings

Basic Product	LE	D				Watts Saved	RT6 Energy	RT6 Life
Description	Lumens	Life	Traditional Lamp Types	Lumens	Life	With RT6	Savings*	Benefit
RT5/6 9W	625	11,000	Incandescent 65WBR30	640	2000	56	\$67	5.5X


* Based on \$0.11/kWh over 11,000 hours life.

Application Information

Application Notes

- 1. Operating temperature range between -40°F and 104°F (-40°C and 40°C).
- 2. Suitable for indoor and outdoor dry, damp and wet locations
- 3. Suitable for dimmers or in housings controlled by a dimmer. For a list of compatible dimmers, please refer to www.sylvania.com.
- 4. Not intended for use with emergency light fixtures or exit lights.
- 5. For use in housings that can structurally support a lamp weighing one pound.
- 6. RT5/6 designed to install in standard 5" and 6" insulated and non-insulated housings. For a list of compatible housings, please refer to www.sylvania.com.
- 7. For detailed warranty information, please refer to www.sylvania.com.


Assembly Diagram





Accessories

 Retrofit Band (For 6" housing models Progress Lighting P87-AT and Lightolier 1104IC)


 70663
 RT6/RETROFITBAND (sold separately)















RT5/6 Retrofit Trim (For non-Gimbal only, can be used with RT5/6 and RT6)

75095	RT/5/6/TRIM/DKBZ	
75097	RT/5/6/TRIM/BLK	
75098	RT/5/6/TRIM/ORBZ	
75099	RT/5/6/TRIM/SN	



Photometric Information





Illuminance at Distance

OSRAM SYLVANIA Inc. 200 Ballardvale Street Wilmington, MA 01887 USA Phone 1-800-LIGHTBULB (1-800-544-4828) www.sylvania.com

SYLVANIA is a registered trademark of OSRAM SYLVANIA Inc. ENERGY STAR is a registered trademark of the U.S. Government. Specifications subject to change without notice.



/sylvania

