



## Part Number: 76404TS

MachFlex™ Continuous 300V Data, (4 pr) 28 AWG (7x36) TC, PVC/PVC, Foil+TC Braid Shld, AWM, CE, CM

[Request Sample](#)

### Product Description

Four 28 AWG pairs stranded (7x36) tinned copper conductors, twisted pairs, lubricated semi-rigid PVC insulation, overall foil plus tinned copper braid shield (85% coverage), oil-resistant PVC jacket.

### Technical Specifications

#### Physical Characteristics (Overall)

##### Conductor

Element	AWG	Stranding	Material	No. of Pairs
Conductor	28	7x36	TC - Tinned Copper	4

Conductor Count:	8
Total Number of Pairs:	4
Conductor Size:	28 AWG

##### Insulation

Element	Material	Nominal Diameter	Nominal Wall Thickness
Conductor	PVC - Polyvinyl Chloride	0.035 in	0.010 in

##### Outer Shield Material

Type	Material	Coverage [%]	Drainwire Material	Drainwire AWG
Tape	Aluminum/Mylar	100 %	TC - Tinned Copper	26
Braid	TC - Tinned Copper	85 %		

##### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.256 in	0.040 in

#### Electrical Characteristics

##### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
67 Ohm/1000ft	3.7 Ohm/1000ft

##### Capacitance

Nom. Capacitance Conductor to Conductor
21.0 pF/ft

Shielding:	Foil + Braid(s)
------------	-----------------

##### Inductance

Nominal Inductance
.22 µH/ft

##### Impedance

Nominal Characteristic Impedance
90 Ohm

##### Voltage

UL Voltage Rating
300 V

## Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-10°C To 105°C (Static), 5°C To 105°C (Flexing)

## Mechanical Characteristics

Flex Cycle Rating:	6 Million Cycles
Bulk Cable Weight:	38 lbs/1000ft
Max Recommended Pulling Tension:	17.8 lbs
Min Bend Radius (Continuous Flexing):	3.9 in
Min Bend Radius/Minor Axis:	2.6 in

## Standards

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CMG
UL AWM Style:	AWM 2661, AWM 10002
CSA AWM Specification:	AWM I/II A/B

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes

## Suitability

Suitability - Sunlight Resistance:	Yes
------------------------------------	-----

## Flammability, LS0H, Toxicity Testing

CSA Flammability:	FT4
UL voltage rating:	300 V RMS

## Part Number

### Variants

Item #	Color
76404TS 008100	Gray
76404TS 0081000	Gray

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.