

Datasheet

Foot switch, light weight polymeric housing



RS Article No.1253717

Specifications:

Operating Frequency:	60 ops/min
Insulation Resistance:	>100MΩ@500V DC
Contact Resistance:	<25mΩ (initial)
Rated Current/Voltage:	15A, 1/2HP, 125/250VAC
Dielectric Strength:	1000VAC for 1 min between current carrying parts 2500VAC for 1 min between non-current carrying parts
Service Life:	Mechanically 1X10 ⁶ Electrically 5X10 ⁵
Operating Temperature:	-20~+80°C (-4~176°F)
Degree of Protection:	IP20
Size (LXWXH):	100x75x33mm

Features:

- Robust glass fiber reinforced plastic
- UL/CSA/CE/CCC Certified
- Galvanically separated contacts
- SPDT TYPE
- Momentary type

RS PRO
Stock No. 125-3717

