



Figure similar

MLFB-Ordering data

6SL3246-0BA22-1PA0

Client order no. :

Item no. :

Order no. :

Consignment no. :

Offer no. :

Project :

Remarks :

### Electrical data

#### Operating voltage via

The Power Module	DC 24 V
External power supply	DC 20 ... 29 V
Max. power consumption	2.00 A
Power loss	12.00 W

### Inputs / outputs

#### Standard digital inputs

Number	15
Switching level: 0→1	11 V
Switching level: 1→0	5 V

#### Fail-safe digital inputs

Number	3 (Use of 2 × DI Standard)
--------	----------------------------

#### Digital outputs

Number as relay changeover contact	2
------------------------------------	---

Output (resistive load)	DC 30 V, 1 A
-------------------------	--------------

Output (resistive load)	DC 30 V, 1 A
-------------------------	--------------

#### Analog / digital inputs

Number	2 (Differential input)
--------	------------------------

#### Analog outputs

Number	2 (Non-isolated output)
--------	-------------------------

### Connections

#### Signal cable

Conductor cross-section	0.05 ... 1.50 mm <sup>2</sup> (30 ... 16 AWG)
-------------------------	---

### Ambient conditions

#### Ambient temperature

Operation	-10 ... 50 °C (14 ... 122 °F)
Storage	-40 ... 70 °C (-40 ... 158 °F)

#### Relative humidity

Max. operation	95 %
----------------	------

### Communication

Communication	PROFIBUS DP
---------------	-------------

### Closed-loop control techniques

V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	Yes
Encoderless torque control	Yes
Torque control, with encoder	Yes

### Standards

Compliance with standards	UL, cUL, CE, C-Tick (RCM)
---------------------------	---------------------------

CE marking	Low-voltage directive 2006/95/EC
------------	----------------------------------

### Mechanical data

Degree of protection	IP20
Net weight	0.61 kg
Width	73.0 mm
Height	199.0 mm
Depth	67.0 mm