


## N ATTENUATOR 3 DB 18 GHZ 2W

**R414.703.161**Series: **ATTENUATOR** 





Scale 1:1



All dimensions are in mm.



| COMPONENTS  | MATERIALS  | PLATING(μm)  |
|---|--|--|
| BODY MALE CENTER CONTACT FEMALE CENTER CONTACT OUTER CONTACT INSULATOR GASKET SUBSTRATE RESISTOR OTHERS PARTS | STAINLESS STEEL BERYLLIUM COPPER BERYLLIUM COPPER PTFE SILICONE RUBBER ALUMINA THIN FILM | PASSIVATED GOLD 1.2 OVER NICKEL 2 GOLD 1.2 OVER NICKEL 2 |

Issue: 0839 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary.



# N ATTENUATOR 3 DB 18 GHZ 2W

**R414.703.161**Series: ATTENUATOR

#### **ELECTRICAL CHARACTERISTICS**

| Frequency (GHz) | DC - 4 | 4 - 8 | 8 - 12.4 | 12.4 - 18 |
|-----------------|--------|-------|----------|-----------|
| V.S.W.R (≤)     | 1.15   | 1.20  | 1.25     | 1.35      |
| Deviation(±dB)  | 0.40   | 0.40  | 0.40     | 0.40      |

| DC - 18 | GHz                   |
|---------|-----------------------|
| 50      | Ω                     |
| 3       | dB                    |
| 100     | W                     |
| 2       | W (Free Air Cooled)   |
|         | W (Conduction Cooled) |
|         | 50                    |


### **MECHANICAL CHARACTERISTICS**

| Connectors |           |  |
|------------|-----------|--|
| Weight     | 60.0400 g |  |

#### **ENVIRONMENTAL CHARACTERISTICS**

| Operating temperature range | °C |
|-----------------------------|----|
| Storage temperature range   | °C |

#### Power derating Versus temperature



## **SPECIFICATION**

### **OTHER CHARACTERISTICS**

