



2017

Like Us On
facebook 

wiha 

Tools that work for you





Professional TorqueControl Screwdrivers




Complete TorqueControl Program




Wiha TorqueFix Wing Handles & Blades

DESCRIPTION	Page
 TorqueFix Handle	4
 Hex Metric Blades	4
 TORX Blades	4
 TORXPlus Blades	4



Wiha TPMS Install / Repair Kit

DESCRIPTION	Page
 TPMS Set	4



Wiha TorqueControl Tools

DESCRIPTION	Page
 TorqueFix Handle	5
 TorqueVario Handle	5
 TorqueVario Handle (Newton Meter Scale)	5
 Standard Blades Slotted, Phillips, Torx®, TorxPlus®, Hex	6
 MicroBits Slotted, Phillips, Torx®, Security Torx® Hex, Security Hex, Pentalobe & Nut Setters	9
 TorqueControl Sets	10-11



Wiha TorqueControl Blades & Bits

DESCRIPTION	Page
 Standard Blades Slotted, Phillips, Torx®, TorxPlus®, Hex	6
 MicroBits Slotted, Phillips, Torx®, Security Torx® Hex, Security Hex, Pentalobe & Nut Setters	9



Wiha EasyTorque Handles

DESCRIPTION	Page
 EasyTorque Handles	7
 EasyTorque TORX	7
 EasyTorque TORXPlus	7





Wiha iTorque Handles & Sets

DESCRIPTION	Page
 iTorque Handles	8
 iTorque Sets	8

Wiha TorqueControl Accessories

DESCRIPTION	Page
 TorqueControl Adapters	6-7
 Torque Cable Key	7

Wiha Torque SlimLine Insulated Tools

DESCRIPTION	Page
 TorqueVario Handle	12
 Insulated Blade Holder	13
 Insulated SlimLine Blades Slotted, Phillips, Terminal, TORX, Square	13
 Ins. Torque SlimLine Sets	12



Wiha TorqueFix Wing Keys Handles & Blades

- Audible Click At Torque
- Replaceable Blades
- +/- 6% Repeatability
- Extremely Compact
- Quick Turning Zone



Low profile
for easy access

Small &
Compact

Very slim blade diameter for
hard to reach screws

Torque tool for very tight
machine assembly spaces



EN ISO 6798,
BS EN 26789, ASME
B107.14M

+/- 6% Accuracy



Includes Calibration
Certificate

283 TorqueFix Wing Handles

Audible & perceptible click when torque setting
has been attained.

Item No.	Nm	mm	Inch	pkg.	lbs.
28349	0.5	68	2.7	1	.28
28351	0.6	68	2.7	1	.28
28352	0.9	68	2.7	1	.28
28353	1.1	68	2.7	1	.28
28354	1.2	68	2.7	1	.28
28355	1.4	68	2.7	1	.28
28356	2.0	68	2.7	1	.28
28357	2.5	68	2.7	1	.28
28358	3.0	68	2.7	1	.28
28359	3.8	68	2.7	1	.28
28360	4.0	68	2.7	1	.28



283 TORX® Blades For TorqueFix

Wing Handles CVM steel, through-hardened,
titanium silver.

Item No.	Size	Max Nm	Inch	pkg.	lbs.
28374	T6	0.6	3.0	1	.03
28375	T7	0.9	3.0	1	.03
28376	T8	1.3	3.0	1	.03
28377	T9	2.5	3.0	1	.03
28378	T10	3.8	3.0	1	.03
28379	T15	5.5	3.0	1	.03
28380	T20	8.0	3.0	1	.03
28381	T25	8.0	3.0	1	.03



283 TORXPlus® Blades For TorqueFix

Wing Handles CVM steel, through-hardened,
titanium silver.

Item No.	Size	Max Nm	Inch	pkg.	lbs.
28382	IP6	0.8	3.0	1	.03
28383	IP7	1.3	3.0	1	.03
28384	IP8	2.0	3.0	1	.03
28385	IP9	3.0	3.0	1	.03
28386	IP10	4.5	3.0	1	.03
28387	IP15	6.6	3.0	1	.03
28388	IP20	8.0	3.0	1	.03
28389	IP25	8.0	3.0	1	.03



283 Hex Metric Blades For TorqueFix

Wing Handles CVM steel, through-hardened,
titanium silver.

Item No.	Size	Max Nm	Inch	mm	lbs.	pkg.
28361	1.5	0.9	3.0	75	.03	1
28362	2.0	1.8	3.0	75	.03	1
28363	2.5	3.8	3.0	75	.03	1
28364	3.0	5.5	3.0	75	.03	1
28365	4.0	8.0	3.0	75	.03	1



Wiha Adjustable TorqueControl Tools

Wiha TorqueControl Screwdrivers

- *TorqueFix* factory preset torque
- *TorqueVario* adjustable torque drivers

molded cushion grip two component handles allow for maximum achievable torque to be reached with comfort.

Precise repeatability!

All TorqueFix & TorqueVario tools are tested and comply with:

- **EN ISO 6798**
- **BS EN 26789**
- **ASME B107.14M**

Each tool has unique serial number and certificate of calibration

Whether it's TorqueVario-S or TorqueFix - Wiha has a torque screwdriver to cover almost every application



+/-6% accuracy tolerance
Certificate of calibration



Direct Reading Scale



+/-6% accuracy tolerance
Certificate of calibration



+/-6% accuracy tolerance
Certificate of calibration

285 TorqueFix, With Wiha-SoftFinish®

Handle Fixed Torque value pre-set. Tested in accordance with EN ISO 6798, BS EN 26789, ASME B107.14M, tolerance +/- 6%. Audible & perceptible click when pre-set torque has been attained. Automatically resets for next torque cycle; 50% greater reverse torque.

Item No.	Pre-Sets		Nm	mm	Inch	lbs.	pkg.
	oz.	lbs.					
28503	80	5	0.56	112	4.4	.16	1
28505	120	7.5	0.84	112	4.4	.15	1
28507	160	10	1.12	119	4.7	.28	1
28509	200	12.5	1.41	119	4.7	.27	1
28511	240	15	1.69	119	4.7	.27	1
28513	320	20	2.25	119	4.7	.28	1
28515	400	25	2.82	126	4.9	.37	1
28517	480	30	3.39	126	4.9	.37	1
28518	560	35	3.95	126	4.9	.37	1
28519	640	40	4.52	126	4.9	.37	1
28521	800	50	5.65	132	5.2	.52	1
28523	960	60	6.78	132	5.2	.52	1
28525	1120	70	7.91	132	5.2	.52	1

285 Adjustable TorqueVario With Direct Reading Scale

EN ISO 6798, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

Item No.	Range	Increments	Pkg. 1	
			mm	lbs.
28501*	15 - 80(in/oz)	2.5 In.oz.	127	.22
28502	5 - 10	.5 In.lbs.	127	.41
28504	7.5 - 20	.5 In.lbs.	131	.50
28506	10 - 50	2 In.lbs.	138	.59
28508	20 - 70	2 In.lbs.	142	.74

* 28501 +/- 10% (This unit only)*

285 Adjustable TorqueVario-S Handle - In Newton Meter Scale

EN ISO 6798, BS EN 26789, ASME B107.14M. Ergo molded multi-component handle, light & compact. Handle sizes proportioned to optimize torque range. Audible & perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

Item No.	Newton Meter Scale	Increments	Pkg. 1	
			mm	lbs.
28550*	0.1 - 0.6Nm	.02 Nm	127	.35
28551	0.4 - 1.0Nm	.05 Nm	127	.35
28552	0.8 - 2.0Nm	.10 Nm	131	.45
28553	0.8 - 5.0Nm	.20 Nm	138	.55
28655	2.0 - 7.0Nm	.25 Nm	142	.70

* +/- 10% (This unit only)



All TorqueVario models include Torque setting adjustment tool

Wiha TorqueControl Blades - For Easy Torque, TorqueFix & TorqueVario Handles



285 Slotted Interchangeable Blades For TorqueFix & TorqueVario Slotted tip blades on narrow 5/32 Hex shafts. High alloy chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Item				Max.		
No.	mm	Inch	mm	lbs.	Nm	pkg.
28534	1.5	.059	175	.07	0.15	1
28535	2.0	.078	175	.07	0.4	1
28536	2.5	.098	175	.07	0.4	1
28537	3.0	.118	175	.07	0.6	1
28538	3.5	.139	175	.07	1.1	1
28539	4.0	.157	175	.07	2.5	1



285 Phillips Interchangeable Blades For TorqueFix & TorqueVario Phillips tip blades on narrow 5/32 Hex shafts. High alloy chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Item				Max.		
No.	Size	mm	mm	lbs.	Nm	pkg.
28540	000	175	4.0	.07	0.4	1
28541	00	175	4.0	.07	0.4	1
28542	0	175	4.0	.07	0.9	1
28543	1	175	4.0	.07	3.8	1
28544	2	175	4.0	.07	5.5	1



285 TORX® Interchangeable Blades For TorqueFix & TorqueVario TORX® tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item				Max.		
No.	Size	mm	mm	lbs.	Nm	pkg.
28561	T5	175	4.0	.07	0.4	1
28562	T6	175	4.0	.07	0.6	1
28563	T7	175	4.0	.07	0.9	1
28564	T8	175	4.0	.07	1.3	1
28565	T9	175	4.0	.07	2.5	1
28566	T10	175	4.0	.07	3.8	1
28567	T15	175	4.0	.07	5.5	1
28568	T20	175	4.0	.07	8.0	1
28569	T25	175	4.0	.07	8.0	1



285 Hex Inch Interchangeable Blades For TorqueFix & TorqueVario Hex tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item				Max.	
No.	Inch	mm	lbs.	Nm	pkg.
28555	.050	175	.07	.4	1
28556	1/16	175	.07	.9	1
28557	5/64	175	.07	1.8	1
28558	3/32	175	.07	1.8	1
28559	7/64	175	.07	3.8	1
28560	1/8	175	.07	5.5	1
28587	9/64	175	.07	8.0	1
28588	5/32	175	.07	8.0	1



285 Hex Metric Interchangeable Blades For TorqueFix & TorqueVario Hex tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item				Max.	
No.	mm	mm	lbs.	Nm	pkg.
28545	1.5	175	.07	0.9	1
28546	2.0	175	.07	1.8	1
28547	2.5	175	.07	3.8	1
28548	3.0	175	.07	5.5	1
28549	4.0	175	.07	8.0	1



285 TORXPlus® Blades For TorqueFix & TorqueVario TORXPlus® tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item				Max.		
No.	Size	mm	mm	lbs.	Nm	pkg.
28571	IP5	175	4.0	.07	0.5	1
28572	IP6	175	4.0	.07	0.8	1
28573	IP7	175	4.0	.07	1.3	1
28574	IP8	175	4.0	.07	2.0	1
28575	IP9	175	4.0	.07	3.0	1
28576	IP10	175	4.0	.07	4.5	1
28577	IP15	175	4.0	.07	6.6	1
28578	IP20	175	4.0	.07	8.0	1
28579	IP25	175	4.0	.07	8.0	1



285 MagicSpring TORX® Interchangeable Blades For TorqueFix & TorqueVario blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item				Max.		
No.	Size	mm	mm	lbs.	Nm	pkg.
28512	T6	175	4.0	.07	0.6	1
28527	T7	175	4.0	.07	0.9	1
28528	T8	175	4.0	.07	1.3	1
28529	T9	175	4.0	.07	2.5	1
28530	T10	175	4.0	.07	3.8	1
28531	T15	175	4.0	.07	5.5	1
28532	T20	175	4.0	.07	8.0	1
28533	T25	175	4.0	.07	8.0	1



286 MagicSpring TORXPlus® Interchangeable Blades For TorqueFix & TorqueVario blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item				Max.		
No.	Size	mm	mm	lbs.	Nm	pkg.
28611	IP6	175	4.0	.07	0.8	1
28612	IP7	175	4.0	.07	1.3	1
28613	IP8	175	4.0	.07	2.0	1
28614	IP9	175	4.0	.07	3.0	1
28616	IP10	175	4.0	.07	4.5	1
28617	IP15	175	4.0	.07	6.6	1
28618	IP20	175	4.0	.07	8.0	1
28619	IP25	175	4.0	.07	8.0	1

*None of the blades featured on this page will function in a TorqueVario Insulated Handle

Wiha TorqueControl Adapters



28882 ESD Safe Bit Holder Adapter For 1/4" Drive Bits

Shaft CVM steel, hardened, corrosion protected. (Not for use in Insulated handles)

Item				Max.	
No.	Size	mm	mm	lbs.	pkg.
28882	1/4	162	4.0	.09	1








Wiha Torque Cable Keys

Torque handles recommended
#28552 & #28504










286 Torque Cable Key For Threaded Hex Connectors

For torque controlled fastening of cable plug connectors with Hex heads. Used with Wiha-TorqueControl Screwdrivers.

Item					Max 		
No.	Size	mm	mm	mm	Nm	lbs.	pkg.
28620	8mm	4.0	78	218	1.0	.06	1
28622	9mm	4.0	78	218	1.0	.06	1
28624	11mm	4.0	78	218	1.5	.06	1
28626	12mm	4.0	78	218	1.5	.06	1
28627	13mm	4.0	78	218	1.5	.06	1
28629	14mm	4.0	78	218	1.5	.06	1
28632	17mm	4.0	78	218	1.5	.06	1
28633	18mm	4.0	78	218	1.5	.06	1
28637	22mm	4.0	90	233	2.0	.10	1
28638	24mm	4.0	90	233	2.0	.10	1



28644 Torque Cable Key For Threaded Hex Connectors - Inch

Item					Max 		
No.	Size	mm	mm	mm	Nm	lbs.	pkg.
28644	1/2"	4.0	78	218	1.5	.06	1

easyTorque Control Handles

"easy" Torque

- Audible Click At Torque
- Replaceable Blades
- +/- 10% Repeatability
- Improve Productivity
- Reduces Waste
- Controls Costs
- Save Time!



Each tool factory preset

Torque accuracy of +/- 10% to 5000 cycles

Economical Torque Control for tooling assembly and repair


Reverse torque is 50% greater for easy removal using same tool

Uses 285 Series interchangeable blades on pg. 6



292 easyTorque Screwdriver Handle

easyTorque value pre-set. Release accuracy +/- 10%. SoftFinish cushion grip handle for good power transfer.





Item	Pre-Sets					
No.	Inch/lbs.	Nm	mm	Inch	lbs.	pkg.
29205	4.4	0.5	130	5.1	.20	1
29206	5.3	0.6	130	5.1	.20	1
29209	8.0	0.9	130	5.1	.20	1
29211	9.7	1.1	130	5.1	.20	1
29212	10.6	1.2	130	5.1	.20	1
29214	12.4	1.4	130	5.1	.20	1
29220	17.7	2.0	130	5.1	.20	1
29225	22.1	2.5	130	5.1	.20	1
29230	26.6	3.0	130	5.1	.20	1
29238	33.6	3.8	130	5.1	.20	1
29241	35.4	4.0	130	5.1	.20	1
29245	39.8	4.5	130	5.1	.20	1
29251	44.2	5.0	130	5.1	.20	1

* No Calibration Certificates



292 easyTorque Screwdriver Handle With TORX® Blades easyTorque value pre-set.

Release accuracy +/- 10%. Internal mechanism clicks when torque value has been attained. Cushion grip comfortable handle for good power transfer.





Item		Pre-Sets			
No.	Size	Inch/lbs.	Nm	lbs.	pkg.
29232	T5	4.4	0.5	.24	1
29233	T6	5.3	0.6	.24	1
29234	T7	8.0	0.9	.24	1
29236	T8	10.6	1.2	.25	1
29237	T9	12.4	1.4	.25	1
29239	T10	17.7	2.0	.26	1
29242	T15	26.6	3.0	.26	1
29243	T20	35.4	4.0	.26	1
29244	T25	44.2	5.0	.28	1

* No Calibration Certificates



292 easyTorque Screwdriver Handle With TORXPlus® Blades easyTorque value pre-set. Release accuracy +/- 10%.

Internal mechanism clicks when torque value has been attained. Cushion grip comfortable handle for good power transfer.

Item		Pre-Sets			
No.	Size	Inch/lbs.	Nm	lbs.	pkg.
29246	IP5	4.4	0.5	.24	1
29247	IP6	5.3	0.6	.24	1
29248	IP7	8.0	0.9	.24	1
29249	IP8	10.6	1.2	.25	1
29252	IP9	12.4	1.4	.25	1
29253	IP10	17.7	2.0	.26	1
29254	IP15	26.6	3.0	.26	1
29255	IP20	35.4	4.0	.26	1
29256	IP25	44.2	5.0	.28	1






* No Calibration Certificates

Wiha TorqueControl Adapters

Adapters For TorqueFix™ & TorqueVario™








28581 Bit Holder Adapter For 1/4" Drive Bits Shaft CVM steel, hardened, corrosion protected. (Not for use in Insulated handles)

Item					
No.	Size	mm	mm	lbs.	pkg.
28581	1/4	149	4.0	.09	1








28582 Square Drive Adapter For 1/4" Sockets Shaft CVM steel, hardened, corrosion protected. (Not for use in Insulated handles)

Item					
No.	Size	mm	mm	lbs.	pkg.
28582	1/4	145	4.0	.08	1



28583 Adapter Blade For 4mm MicroBits Shaft CVM steel, hardened, corrosion protected. (Not for use in Insulated handles)

Item					
No.	Size	mm	mm	lbs.	pkg.
28583	4.0	149	4.0	.09	1



Wiha TorqueControl Adjustable iTorque

iTorque Screwdrivers

- Metric (Nm) & Inch (In-lbs / oz)
- Built in click counter
- Auto shut off
- Fast adjusting
- Cycle Counter
- Accurate +/- 6%



Digital Torque Control

Interchangeable blades or bits

With Certificate of Calibration Included



4mm bit holder included

288 iTorque Screwdriver Handles

EN ISO 6798, BS EN 26789, ASME B107.14M. Handle reads Nm & Inch/lbs. with built in click counter. Fast adjusting. Accurate +/- 6% Each iTorque handle includes a 4mm bit holder.

Item No.	Adjustable Maximum Torque	Adjustable	pkg. 1		
			mm	Inch	lbs.
28886	60-210(in/oz.)	40-150(Ncm)	134	5.3	.44
28887	7-26 in/lbs.	0.8-3.0 Nm	134	5.3	.44
28888	9-50 in/lbs.	1.0-6.0 Nm	134	5.3	.44

* Calibration Certificates Included



Quick Adjusting

Digital Display

Push Button Start Push Button Conversion

Fast Conversion Nm to In/lbs.

With Certificate of Calibration



52 Pc. Set

28891 52 Piece iTorque Bit Set, In Metal Storage Box Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable iTorque handle 60-210 in/oz. 40-150 Ncm, 50 insert bits & 1/4" bit holder.

Item	Slotted: 4.5, 5.5, 6.5, 8.0mm
No.	Phillips: #0, #1, #2, #3
28891	TORX®: T6, T7, T8, T9, T10, T15, T20, T25, T27, T3
lbs.	Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 2.56 9/64, 5/32, 3/16"
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm
	Pozidriv: #0, #1, #2, #3
	Torq Set: #4, #5, #6, #8
	Square: #1, #2, #3
	Triwing: #0, #1, #2, #3, #4
	iTorque Handle Range 60 - 210 Inch/oz.
	28581 - 1/4" Bit Holder

With Certificate of Calibration



52 Pc. Set

28892 52 Piece iTorque Bit Set, In Metal Storage Box Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable iTorque handle 7-26 in/lbs. 0.8-3.0 Nm, 50 insert bits & 1/4" bit holder.

Item	Slotted: 4.5, 5.5, 6.5, 8.0mm
No.	Phillips: #0, #1, #2, #3
28892	TORX®: T6, T7, T8, T9, T10, T15, T20, T25, T27, T3
lbs.	Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 2.57 9/64, 5/32, 3/16"
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm
	Pozidriv: #0, #1, #2, #3
	Torq Set: #4, #5, #6, #8
	Square: #1, #2, #3
	Triwing: #0, #1, #2, #3, #4
	iTorque Handle Range 7 - 26 Inch/lbs.
	28581 - 1/4" Bit Holder

With Certificate of Calibration



52 Pc. Set

28893 52 Piece iTorque Bit Set, In Metal Storage Box Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable iTorque handle 9-50 in/lbs. 1.0-6.0 Nm, 50 insert bits & 1/4" bit holder.

Item	Slotted: 4.5, 5.5, 6.5, 8.0mm
No.	Phillips: #0, #1, #2, #3
28893	TORX®: T6, T7, T8, T9, T10, T15, T20, T25, T27, T3
lbs.	Hex Inch: 1/16, 5/64, 3/32, 7/64, 1/8, 2.61 9/64, 5/32, 3/16"
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm
	Pozidriv: #0, #1, #2, #3
	Torq Set: #4, #5, #6, #8
	Square: #1, #2, #3
	Triwing: #0, #1, #2, #3, #4
	iTorque Handle Range 9 - 50 Inch/lbs.
	28581 - 1/4" Bit Holder

Wiha SYSTEM 4 Micro Bits



750 SYSTEM 4 Slotted Bits High alloy CVM steel, hardened, on 4 mm hex stock.

Item				
No.	mm	mm	Inch	lbs.
75008	0.8	28	1.1	.01
75012	1.2	28	1.1	.01
75015	1.5	28	1.1	.01
75018	1.8	28	1.1	.01
75020	2.0	28	1.1	.01
75025	2.5	28	1.1	.01
75030	3.0	28	1.1	.01
75035	3.5	28	1.1	.01
75040	4.0	28	1.1	.01



751 SYSTEM 4 Phillips Bits High alloy CVM steel, hardened, on 4 mm hex stock.

Item				
No.	Size	mm	Inch	lbs.
75105	000	28	1.1	.01
75110	00	28	1.1	.01
75115	0	28	1.1	.01
75120	1	28	1.1	.01



753 SYSTEM 4 Hex Inch Bits High alloy CVM steel, hardened, on 4 mm hex stock.

Item				
No.	Inch	mm	Inch	lbs.
75307	.028	28	1.1	.01
75309	.035	28	1.1	.01
75313	.050	28	1.1	.01
75350	1/16	28	1.1	.01
75352	5/64	28	1.1	.01
75354	3/32	28	1.1	.01
75356	7/64	28	1.1	.01
75358	1/8	28	1.1	.01
75360	9/64	28	1.1	.01
75340	5/32	28	1.1	.01



757 SYSTEM 4 TORX® Bits High alloy CVM steel, hardened, on 4 mm stock.

Item				
No.	Size	mm	Inch	lbs.
75701	T1	28	1.1	.01
75702	T2	28	1.1	.01
75703	T3	28	1.1	.01
75704	T4	28	1.1	.01
75705	T5	28	1.1	.01
75706	T6	28	1.1	.01
75707	T7	28	1.1	.01
75708	T8	28	1.1	.01
75709	T9	28	1.1	.01
75710	T10	28	1.1	.01
75715	T15	28	1.1	.01
75720	T20	28	1.1	.01



757 SYSTEM 4 Security TORX® Bits High alloy CVM steel, hardened, on 4 mm stock.

Item				
No.	Size	mm	Inch	lbs.
75727	T7s	28	1.1	.01
75728	T8s	28	1.1	.01
75729	T9s	28	1.1	.01
75735	T10s	28	1.1	.01
75739	T15s	28	1.1	.01
75742	T20s	28	1.1	.01



753 SYSTEM 4 Hex Metric Bits High alloy CVM steel, hardened, on 4 mm hex stock.

Item				
No.	mm	mm	Inch	lbs.
75307	0.7	28	1.1	.01
75309	0.9	28	1.1	.01
75313	1.3	28	1.1	.01
75315	1.5	28	1.1	.01
75320	2.0	28	1.1	.01
75325	2.5	28	1.1	.01
75330	3.0	28	1.1	.01
75340	4.0	28	1.1	.01



753 SYSTEM 4 Metric Security Hex Bits CVM steel, hardened, on 4 mm hex stock.

Item				
No.	mm	mm	Inch	lbs.
75322	2.0	28	1.1	.01
75327	2.5	28	1.1	.01
75332	3.0	28	1.1	.01
75342	4.0	28	1.1	.01

753 SYSTEM 4 Security Hex Inch Bits

Item				
No.	Inch	mm	Inch	lbs.
75362	5/64	28	1.1	.01
75364	3/32	28	1.1	.01
75366	7/64	28	1.1	.01
75368	1/8	28	1.1	.01
75370	9/64	28	1.1	.01
75372	5/32	28	1.1	.01



757 SYSTEM 4 Pentalobe Bits High alloy CVM steel, hardened, on 4 mm stock.

Item				
No.	Size	mm	Inch	lbs.
75743	PL1	28	1.1	.01
75744	PL2	28	1.1	.01
75745	PL3	28	1.1	.01
75746	PL4	28	1.1	.01
75747	PL5	28	1.1	.01
75748	PL6	28	1.1	.01



753 SYSTEM 4 Metric & Inch Nut Setters CVM steel, hardened, on 4 mm hex stock.

Item No.					
		mm	mm	Inch	lbs.
75820		2.0	30	1.2	.01
75821		2.5	30	1.2	.01
75822		3.0	30	1.2	.01
75823		3.5	30	1.2	.01
75824		4.0	30	1.2	.01
75825		4.5	30	1.2	.01
75826		5.0	30	1.2	.01
75827		5.5	30	1.2	.01
Inch		Inch	mm	Inch	lbs.
75810		5/64	30	1.2	.01
75811		3/32	30	1.2	.01
75812		7/64	30	1.2	.01
75813		1/8	30	1.2	.01
75814		9/64	30	1.2	.01
75815		5/32	30	1.2	.01
75816		3/16	30	1.2	.01
75817		7/32	30	1.2	.01

1/4" Drive Micro Bit Tool Adapters



75802 Micro Bit To 1/4" Drive Insert Bit Adapter uses magnets to hold 4mm Micro Bits

Item					
No.	Size	mm	mm	lbs.	
75802		4.0	25	4.0	.01



75803 Long Micro Bit To 1/4" Drive Insert Bit Adapter uses spring clip non-magnetic to hold 4mm Micro Bits

Item					
No.	Size	mm	mm	lbs.	
75803		4.0	38	4.0	.02

Wiha Adjustable TorqueControl Tool Sets In Durable Storage Cases



53 Pc. Set




With Certificate of Calibration



59 Pc. Set



With Certificate of Calibration



59 Pc. Set

With Certificate of Calibration

28595 53 Piece TorqueVario-S Bit Set, In Storage Box Set includes ergonomic multi-component adjustable TorqueVario-S handle, 50 Insert bits, 1/4" Bit holder and Torque adjustment tool.

Item	Slotted: 4.5, 5.5, 6.5, 8.0mm
No.	Phillips: #0, #1, #2, #3
28595	TORX®: T6, T7, T8, T9, T10, T15, T20, T25, T27, T30
lbs.	Hex Inch: 1/16, 5/64, 3/32, 7/64, 2.04 1/8, 9/64, 5/32, 3/16"
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm
	Pozidriv®: #0, #1, #2, #3
	Torq Set: #4, #5, #6, #8
	Square: #1, #2, #3
	Tri-Wing: #0, #1, #2, #3, #4
	28506 - Handle Range 10-50 In/lbs.
	28581 - 1/4" Bit Holder

28589 59 Piece TorqueVario-S Bit Set, In Storage Box Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes 3 ergonomic multi-component adjustable TorqueVario-S handles, 39 Insert bits, 15 Sockets, 1/4" Bit holder, 1/4" Hex to 1/4" Square adapter and Torque adjustment tool.

Item	Slotted: 4.5, 5.5, 6.0mm
No.	Phillips: #0, #1, #2
28589	TORX®: T5, T6, T7, T8, T9, T10, T15, T20, T25, T30
lbs.	Hex Inch: .050, 1/16, 5/64, 3/32, 2.73 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm
	Pozidriv®: #1, #2
	Square: #1, #2, #3
	Inch Sockets: 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 3/8"
	Metric Sockets: 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0mm
	3 Handles: 15 - 80 In/oz., 5 - 10 & 10 - 50 In/lbs.
	1/4" Bit Holder
	1/4" Hex to 1/4" Square adapter

28689 59 Piece Torque Newton Meter Bit Set, In Storage Box Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes 3 ergonomic multi-component adjustable Torque Nm handles, 39 Insert bits, 15 Sockets, 1/4" Bit holder, 1/4" Hex to 1/4" Square adapter and Torque adjustment tool.

Item	Slotted: 4.5, 5.5, 6.0mm
No.	Phillips: #0, #1, #2
28689	TORX®: T5, T6, T7, T8, T9, T10, T15, T20, T25, T30
lbs.	Hex Inch: .050, 1/16, 5/64, 3/32, 2.73 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
	Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm
	Pozidriv®: #1, #2
	Square: #1, #2, #3
	Inch Sockets: 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 3/8"
	Metric Sockets: 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0mm
	3 Handles: 0.1-0.6 Nm, 0.4-1.0 Nm & 1.0-5.0 Nm
	1/4" Bit Holder
	1/4" Hex to 1/4" Square adapter



Wiha Adjustable TorqueControl Tool Sets In Durable Storage Box



With Certificate of Calibration

28590 24 Pc. TorqueVario-S Micro-Bit Set

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder & Torque adjustment tool. Packed in a compact durable storage box.


Item No.	Slotted: 1.5, 2.0, 3.0, 4.0mm
No.	Phillips: #00, #0, #1
28590	TORX®: T6, T7, T8, T9, T10, T15
	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32
lbs.	1.35
	28504 - Handle Range 7.5 - 20 In/lbs.



With Certificate of Calibration

28593 24 Pc. TorqueVario-S Micro-Bit Set

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder & Torque adjustment tool. Packed in a compact durable storage box.

Item No.	Slotted: 1.5, 2.0, 3.0, 4.0mm
No.	Phillips: #00, #0, #1
28593	TORX®: T6, T7, T8, T9, T10, T15
	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32
lbs.	1.35
	28501 - Handle Range 15-80 In/oz. (+/- 10%)

Wiha TorqueControl Sets In Durable Canvas Pouch



28596 8 Piece TorqueControl Set With Slotted & Phillips Blades Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 6 blades & Torque adjustment tool. Packed in a durable canvas pouch.


Item No.	28596
Slotted:	2.5, 3.0, 3.5, 4.0mm
	Phillips: #0, #1
lbs.	1.0
	28504 - Handle Range 7.5 - 20 In/lbs.

With Certificate of Calibration



28600 20 Piece TorqueControl Set With Slotted, Phillips, TORX®, Hex Inch Blades

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 18 blades & Torque adjustment tool. Packed in a durable canvas pouch.

Item No.	28600
Slotted:	2.5, 3.5, 4.0mm
Phillips:	#0, #1, #2
	TORX®: T7, T8, T9, T10, T15, T20
lbs.	1.38
	28506 - Handle Range 10 - 50 In/lbs.

With Certificate of Calibration



28597 8 Pc. TorqueControl Set With TORX® Blades

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M

With Certificate of Calibration



28598 8 Piece TorqueControl Set With TORXPlus® Blades Certified to EN ISO 6798, BS EN 26789, ASME B107.14M

Item No.	TORXPlus®	lbs.
28598	IP7, IP8, IP9, IP10, IP15, IP20	1.00
	28506 - Handle Range 10 - 50 In/lbs.	

With Certificate of Calibration



28599 14 Piece TorqueControl Set With TORX® & TORXPlus® Blades Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes Ergonomic multi-component adjustable TorqueVario-S handle, 12 blades & Torque adjustment tool. Packed in a durable canvas pouch.

Item No.	TORXPlus®	lbs.
28599	IP7, IP8, IP9, IP10, IP15, IP20	1.25
	TORX®: T7, T8, T9, T10, T15, T20	
	28506 - Handle Range 10 - 50 In/lbs.	

With Certificate of Calibration



Wiha Insulated TorqueControl Tools

Includes Certificate



1000V

287 Insulated TorqueVario-S, With Window Scale Insulation up to 1000Volt EN ISO, BS EN, ASME, VDE, ASTM & NFPA70E standards, +/- 6% Accuracy. Handle sizes proportioned to optimize torque range. Audible and perceptible click when torque setting has been attained. Includes *SlimLine* blade holder.

Item No.	Range	Inch	lbs.	Increments	mm	lbs.	pkg.
28724	5 - 18	.5	In.lbs.	131	.43	1	
28726	10 - 50	2	In.lbs.	138	.40	1	
28727	20 - 70	2	In.lbs.	142	.69	1	

Each TorqueVario handle has unique serial number and certificate of calibration

287 Insulated TorqueVario-S Handle - In Newton Meter Scale Includes *SlimLine* blade holder.

Item No.	Range	Nm	mm	lbs.	pkg.
28734	0.6 - 2.0	131	.45	1	
28736	1.0 - 5.0	138	.45	1	
28737	2.0 - 8.0	142	.72	1	

Wiha Insulated Torque Ratchet Wrenches



1000V

301 Insulated Torque Ratchet Wrenches, 1/4, 3/8, 1/2" Drives Insulated to EN/IEC 60900:2004, ASTM F1505-10, CSA Standards Visible reading scale for easy reading and adjustment. Locking endcap Torque adjuster for easy adjustment. Accuracy +/- 10%. Dual scale reading Ft. lbs. / Nm.

Item No.	OAL	OAL	Inch	Nm	lbs.
30114	1/4"	210	8.25	5-25	1.02
30138	3/8"	370	14.5	5-50	2.72
30152	1/2"	530	21.0	40-220	3.64

Insulated Torque & SlimLine Tool Sets

1000V



28791 8 Piece Insulated TorqueControl Set With Slotted & Phillips SlimLine Blades

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes Insulated multi-component adjustable TorqueVario-S handle, 5 *SlimLine* blades, *SlimLine* blade holder & Torque adjustment tool.

Item No.	Slotted	Phillips	Blade Holder
28791	3.0, 4.0, 5.5mm	#1, #2	#1, #2
28726	Handle Range 10-50 Inch/lbs.		
28727	Blade Holder		

With Certificate of Calibration

1000V



28792 16 Piece Insulated TorqueControl Set With SlimLine Blades Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes Insulated multi-component adjustable TorqueVario-S handle, 13 *SlimLine* blades, *SlimLine* blade holder & Torque adjustment tool.

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes Insulated multi-component adjustable TorqueVario-S handle, 13 *SlimLine* blades, *SlimLine* blade holder & Torque adjustment tool.

Item No.	Slotted	Phillips	Terminal Xeno	TORX	Square	Blade Holder
28792	4.0, 5.5, 6.5mm	#1, #2	#1, 2	T8, T10, T15, T20	#1, #2	#1, #2
28727	Handle Range 20-70 Inch/lbs.					
28727	Blade Holder					

With Certificate of Calibration

Wiha Insulated SlimLine Torque Blade Holder

1000V



28350 Insulated SlimLine Torque Blade Holder CVM steel. Through hardened black finish. ClicFix quick release holder securely locks blades.

Item No.	OAL	OAL	Inch	lbs.	pkg.
28350	6.0	170	6.75	.06	1

1000V



28370 Insulated SlimLine Torque Blade Holder CVM steel. Through hardened black finish. Non-locking friction fit blade holder for *SlimLine* Blades.

Item No.	OAL	OAL	Inch	lbs.	pkg.
28370	6.0	170	6.75	.06	1

ESD Safe Adjustable TorqueControl Tools



Includes Certificate

285 ESD Safe TorqueVario-S, With Window Scale EN ISO 6798, BS EN 26789, ASME B107.14M, +/- 6% Accuracy. Ergonomic multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible & perceptible click when torque setting has been attained. With Certificate of accuracy. Pkg. 1

Item No.	Range				
No.	Inch lbs.	Increments	mm	lbs.	pkg.
28522*	15 - 80(in/oz)	2.5 In.oz.	122-127	.33	
28524	5 - 10	.2 In.lbs.	122-127	.34	
28526	7.5 - 20	.5 In.lbs.	126-131	.42	

Item No.	Range				
No.	Nm	mm	Inch	lbs.	pkg.
28500*	.04 - .46	124	4.875"	.35	1

* +/- 10% (This unit only)

Each TorqueVario handle has unique serial number and certificate of calibration



With Certificate of Calibration

28591 24 Piece ESD Safe Adjustable TorqueVario-S Bit Set

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder and Torque adjustment tool, packed in a compact durable storage box.

Item No.	Slotted:	Phillips:	Hex Inch:	Hex Metric:	Pentalobe:
28591	T6, T7, T8, T9, T10, T15	#00, #0, #1	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"	0.7, 0.9, 1.3mm	PL1, PL2, PL3, PL4



288 ESD Safe Slotted Interchangeable Blades For TorqueVario-S Slotted tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item No.	mm	Inch	mm	Nm	lbs.	pkg.
28801	1.5	.059	175	0.15	.07	1
28805	3.0	.118	175	0.6	.07	1
28807	3.5	.139	175	1.1	.07	1
28809	4.0	.157	175	2.5	.07	1



288 ESD Safe Phillips Interchangeable Blades For TorqueVario-S Phillips tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item No.	Size	mm	mm	Nm	lbs.	pkg.
28810	000	175	4.0	0.4	.07	1
28812	00	175	4.0	0.4	.07	1
28814	0	175	4.0	0.9	.07	1
28816	1	175	4.0	3.8	.07	1



With Certificate of Calibration

Packed in a compact durable storage box
+/- 10%

28890 24 Piece TorqueVario-S ESD Safe Micro-Bit Set

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder and Torque adjustment tool.

Item No.	Slotted:	Phillips:	Hex Inch:	Hex Metric:
28890	T6, T7, T8, T9, T10, T15	#00, #0, #1	.050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"	0.7, 0.9, 1.3mm



With Certificate of Calibration

28895 24 Piece ESD Safe Adjustable TorqueVario-S Bit Set

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder and Torque adjustment tool, packed in a compact durable storage box.

Item No.	Slotted:	Phillips:	TORX:	Hex Metric:	Pentalobe:
28895	0.8, 1.2, 1.5, 2.0mm	#000, #00, #0	T1, T2, T3, T4, T5, T6	0.7, 0.9, 1.3mm	PL1, PL2, PL3, PL4




288 ESD Safe TORX Interchangeable Blades For TorqueVario-S TORX tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, hard chromed.





Item No.	Size	mm	mm	Nm	lbs.	pkg.
28825	T5	175	4.0	0.4	.07	1
28826	T6	175	4.0	0.6	.07	1
28827	T7	175	4.0	0.9	.07	1
28828	T8	175	4.0	1.3	.07	1
28829	T9	175	4.0	2.5	.07	1
28830	T10	175	4.0	3.8	.07	1

ESD Safe TorqueControl Tools



 Includes Certificate






285 ESD Safe TorqueVario-S Newton Meter, With Window Scale EN ISO 6798, BS EN 26789, ASME B107.14M, +/- 10% Accuracy. Ergonomic multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible & perceptible click when torque setting has been attained. With Certificate of accuracy.

Item No.	Range				
No.	Nm	mm	Inch	lbs.	pkg.
28500	.04 - .46	124	4.875"	.35	1

ESD TorqueVario handle has unique serial number and certificate of calibration








288 ESD Safe Pentalobe IPR Interchangeable Blades For TorqueVario-S Newton Meter Handle tip blades on narrow 5/32 Hex shafts. High alloy CVM steel, hardened, hard chromed.

Item No.					
No.	Size	mm	mm	lbs.	pkg.
28818	PL1	175	4.0	.07	1



28882 ESD Safe Bit Holder Adapter For 1/4" Drive Bits Shaft CVM steel, hardened, corrosion protected. (Not for use in Insulated handles)

Item No.					
No.	Size	mm	mm	lbs.	pkg.
28882	1/4	162	4.0	.09	1




T-handle TorqueControl Handles



Accuracy Ergonomic multi-component handle, light & compact

Includes Calibration Certificate

289 TorqueFix T-handle EN ISO 6798, BS EN 26789, ASME B107.14M, +/- 6%





Item No.	Torque In-lbs.	Torque Nm	mm x mm			
28931	53.1	6	56 x 120	.81		1
28933	70.8	8	56 x 120	.82		1
28935	88.5	10	56 x 120	.79		1
28937	106.2	12	56 x 120	.79		1
28938	110.6	12.5	56 x 120	.80		1
28939	123.9	14	56 x 120	.80		1

Each TorqueFix T-handle has unique serial number and certificate of calibration



Includes Calibration Certificate

28940 Adjustable TorqueVario STplus T-handle EN ISO 6798, BS EN 26789, ASME B107.14M, +/- 6%







Item No.	Torque Nm	Torque In-lbs.	mm x mm				
No.	Nm	In-lbs.	mm x mm	lbs.	pkg.		
28940	5-14	44.3-123.9	56 x 120	.81		1	

* (1 Nm 8.8507) (Scale is shown in Nm only)

T-handle TorqueControl Blades









289 TORX® Interchangeable Blades For TorqueFix T-Handle TORX® tip blades on 6mm Hex shafts. High alloy CVM steel, hardened, hard chromed.

Item No.						
No.	Size	mm	Inch	mm	lbs.	pkg.
28903	T15	130	5.1	6.0	.10	1
28904	T20	130	5.1	6.0	.10	1
28905	T25	130	5.1	6.0	.11	1
28906	T27	130	5.1	6.0	.11	1
28907	T30	130	5.1	6.0	.11	1
28908	T40	130	5.1	6.0	.11	1








289 TORXPlus® Interchangeable Blades For TorqueFix T-Handle TORXPlus® tip blades on 6mm Hex shafts. High alloy CVM steel, hardened, hard chromed.

Item No.						
No.	Size	mm	Inch	mm	lbs.	pkg.
28910	IP15	130	5.1	6.0	.10	1
28911	IP20	130	5.1	6.0	.10	1
28912	IP25	130	5.1	6.0	.11	1
28913	IP27	130	5.1	6.0	.11	1
28914	IP30	130	5.1	6.0	.11	1
28915	IP40	130	5.1	6.0	.11	1








289 Hex Metric Interchangeable Blades For TorqueFix T-Handle Hex tip blades on 6mm Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item No.					
No.	mm	mm	Inch	lbs.	pkg.
28916	3.0	130	5.1	.11	1
28917	4.0	130	5.1	.11	1
28918	5.0	130	5.1	.11	1
28919	6.0	130	5.1	.11	1









289 Hex Inch Interchangeable Blades For TorqueFix T-Handle Hex tip blades on 6mm Hex shafts. High alloy CVM steel, hardened, satin hard chrome finish.

Item No.					
No.	Inch	mm	Inch	lbs.	pkg.
28920	1/8	130	5.1	.11	1
28921	9/64	130	5.1	.11	1
28922	5/32	130	5.1	.11	1
28923	3/16	130	5.1	.11	1
28924	7/32	130	5.1	.11	1

Wiha T-handle TorqueControl Adapters









289 TorqueFix Adapter For 1/4" & 3/8" Sockets Shaft CVM steel, hardened, corrosion protected.

Item No.						
No.	Size	mm	Inch	mm	lbs.	pkg.
28926	1/4	100	3.9	6.0	.12	1
28927	3/8	100	3.9	6.0	.15	1



28925 TorqueFix Quick Release Bit Holder Shaft CVM steel, hardened, corrosion protected.

Item No.						
No.	Size	mm	Inch	mm	lbs.	pkg.
28925	1/4	125	4.9	6.0	.15	1

Maximum Recommended Torque For Wiha Torque Blades

Tip Size	Style	Maximum Torque	
T5	TORX	.4 Nm	3.5 in.lbs
T6	TORX	.6 Nm	5.31 in.lbs
T7	TORX	.9 Nm	7.9 in.lbs
T8	TORX	1.3 Nm	11.5 in.lbs
T9	TORX	2.5 Nm	22.1 in.lbs
T10	TORX	3.8 Nm	33.6 in.lbs
T15	TORX	5.5 Nm	48.7 in.lbs
T20	TORX	8.0 Nm	70.8 in.lbs
T25	TORX	8.0 Nm	70.8 in.lbs
IP5	TORX Plus	.5 Nm	4.4 in.lbs
IP6	TORX Plus	.8 Nm	7.0 in.lbs
IP7	TORX Plus	1.3 Nm	11.5 in.lbs
IP8	TORX Plus	2.0 Nm	17.7 in.lbs
IP9	TORX Plus	3.0 Nm	26.5 in.lbs
IP10	TORX Plus	4.5 Nm	39.8 in.lbs
IP15	TORX Plus	6.6 Nm	58.4 in.lbs
IP20	TORX Plus	8.0 Nm	70.8 in.lbs
IP25	TORX Plus	8.0 Nm	70.8 in.lbs
1.5	Slotted	.15 Nm	1.3 in.lbs
2.0	Slotted	.4 Nm	3.5 in.lbs
2.5	Slotted	.4 Nm	3.5 in.lbs
3.0	Slotted	.6 Nm	5.31 in.lbs
3.5	Slotted	1.1 Nm	9.7 in.lbs
4.0	Slotted	2.5 Nm	22.1 in.lbs
#000	Phillips	.4 Nm	3.5 in.lbs
#00	Phillips	.4 Nm	3.5 in.lbs
#0	Phillips	.9 Nm	7.9 in.lbs
#1	Phillips	3.8 Nm	33.6 in.lbs
#2	Phillips	5.5 Nm	48.6 in.lbs
1.5	Hex Metric	.9 Nm	7.9 in.lbs
2.0	Hex Metric	1.8 Nm	15.9 in.lbs
2.5	Hex Metric	3.8 Nm	33.6 in.lbs
3.0	Hex Metric	5.5 Nm	48.6 in.lbs
4.0	Hex Metric	8.0 Nm	70.8 in.lbs
.050	Hex Inch	.4 Nm	3.5 in.lbs
1/16	Hex Inch	.9 Nm	7.9 in.lbs
5/64	Hex Inch	1.8 Nm	15.9 in.lbs
3/32	Hex Inch	1.8 Nm	15.9 in.lbs
7/64	Hex Inch	3.8 Nm	33.6 in.lbs
1/8	Hex Inch	5.5 Nm	48.6 in.lbs
9/64	Hex Inch	8.0 Nm	70.8 in.lbs
5/32	Hex Inch	8.0 Nm	70.8 in.lbs

Numerical Index by Item Number

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
28307	13	28374	4	28533	6	28581	7	28805	14
28308	13	28375	4	28534	6	28582	7	28807	14
28309	13	28376	4	28535	6	28583	7	28809	14
28312	13	28377	4	28536	6	28587	6	28810	14
28315	13	28378	4	28537	6	28588	6	28812	14
28317	13	28379	4	28538	6	28589	10	28814	14
28319	13	28380	4	28539	6	28590	11	28816	14
28320	13	28381	4	28540	6	28591	14	28818	15
28321	13	28382	4	28541	6	28593	11	28825	14
28327	13	28383	4	28542	6	28595	10	28826	14
28329	13	28384	4	28543	6	28596	11	28827	14
28330	13	28385	4	28544	6	28597	11	28828	14
28331	13	28386	4	28545	6	28598	11	28829	14
28332	13	28387	4	28546	6	28599	11	28830	14
28333	13	28388	4	28547	6	28600	11	28882	6,15
28334	13	28389	4	28548	6	28611	6	28886	8
28335	13	28500	14,15	28549	6	28612	6	28887	8
28336	13	28501	5	28550	5	28613	6	28888	8
28337	13	28502	5	28551	5	28614	6	28890	14
28338	13	28503	5	28552	5	28616	6	28891	8
28339	13	28504	5	28553	5	28617	6	28892	8
28340	13	28505	5	28555	6	28618	6	28893	8
28341	13	28506	5	28556	6	28619	6	28895	14
28342	13	28507	5	28557	6	28620	7	28903	15
28343	13	28508	5	28558	6	28622	7	28904	15
28346	13	28509	5	28559	6	28624	7	28905	15
28347	13	28511	5	28560	6	28626	7	28906	15
28349	4	28512	6	28561	6	28627	7	28907	15
28350	12	28513	5	28562	6	28629	7	28908	15
28351	4	28515	5	28563	6	28632	7	28910	15
28352	4	28517	5	28564	6	28633	7	28911	15
28353	4	28518	5	28565	6	28637	7	28912	15
28354	4	28519	5	28566	6	28638	7	28913	15
28355	4	28521	5	28567	6	28644	7	28914	15
28356	4	28522	14	28568	6	28655	5	28915	15
28357	4	28523	5	28569	6	28689	10	28916	15
28358	4	28524	14	28571	6	28724	12	28917	15
28359	4	28525	5	28572	6	28726	12	28918	15
28360	4	28526	14	28573	6	28727	12	28919	15
28361	4	28527	6	28574	6	28734	12	28920	15
28362	4	28528	6	28575	6	28736	12	28921	15
28363	4	28529	6	28576	6	28737	12	28922	15
28364	4	28530	6	28577	6	28791	12	28923	15
28365	4	28531	6	28578	6	28792	12	28924	15
28370	12	28532	6	28579	6	28801	14	28925	15

MANUFACTURING
EXCELLENCE
AWARD
BESTES KMU
2014

WIHA – WINNER OF THE
MX AWARD 2014.
GERMANY'S BEST SME.



Like Us On
facebook

wiha 

Tools that work for you



(800) 494-6104
fax: (800) 494-7456
cservice@wihatools.com
www.wihatools.com

Catalog Item No. 99001.wo
version - 6/1/17

Subject to change
without notice

©2017 Willi Hahn Corporation

®Torx is a registered trademark of
Acument Intellectual Properties LLC.



Wiha Quality Tools

1348 Dundas Circle
Monticello, MN 55362
tel: 763.295.6591
fax: 763.295.6598

Wiha Tools Canada Ltd.

www.wihatools.ca
Brampton, ONT L6T 4X4
tel: 866.494.0096 or 763.295.6591
fax: 763.295.6598

To:



99977.wo - Pliers/Crimpers Catalog



99004.wo - Shop Tools Catalog




99914.wo - TORX Catalog



99951.wo - Bits Catalog



99919.wo - Insulated Catalog



99002.wo - Screwdrivers Catalog




99934.wo - Hex Tools Catalog



99006.wo - Tech Tools Catalog



99945.wo - ESD Catalog



91330.wo - Tooling Catalog