


Proximity Sensor SMT-8M-A-PS-24V-E-0,3-M12

Part number: 574337

★ Core product range

FESTO



Data sheet

| Feature | Value |
|--|--|
| Design | for T-slot |
| Based on the standard | EN 60947-5-2 |
| Authorization | RCM Mark c UL us - Listed (OL) |
| CE symbol (see declaration of conformity) | according to EU-EMV guideline |
| Special characteristics | Oil resistant |
| Materials note | Free of copper and PTFE Conforms to RoHS Halogen-free |
| Measured variable | Position |
| Measuring principle | Magneto-resistive |
| Ambient temperature | -40 ... 85 °C |
| Switch output | PNP |
| Switching element function | Normally open contact |
| Switching output repetition accuracy in ± mm | 0.1 mm |
| Switch-on time | ≤ 1.3 ms |
| Switch-off time | ≤ 1.4 ms |
| Max. switching frequency | 180 Hz |
| Max. output current | 100 mA |
| Max. output current in mounting kits | 100 mA |
| Max. contact rating DC | 2.8 W |
| Max. switching capacity DC in mounting kits | 2.8 W |
| Voltage drop | < 1.5 V |
| Short circuit strength | Yes |
| Overload withstand capability | Available |
| Nominal operating voltage DC | 24 V |
| Operating voltage range DC | 5 ... 30 V |
| Polarity protected | for all electrical connections |
| Electrical connection 1, connection type | Cable with plug |
| Electrical connection 1, connection technology | M12x1 A-coded to EN 61076-2-101 |
| Electrical connection 1, number of pins/wires | 3 |
| Electrical connection 1, type of mounting | Screw lock |
| Connector exit direction | axial |
| Test conditions of cable | Bending strength according to Festo standard Test conditions on request Chain link trunking: 5 million cycles, bending radius 28 mm Torsion resistance: > 300,000 cycles, ±270°/0.1 m |
| Cable length | 0.3 m |
| Cable attribute | Energy chain + robot |
| Cable sheath color | Grey |
| Material cable sheath | TPE-U(PUR) |
| Mounting type | Tightened Insertable in slot from above |
| Max. tightening torque | 0.6 Nm |

| Feature | Value |
|--|---|
| Assembly position | Any |
| Product weight | 15.9 g |
| Housing color | Black |
| Material housing | Nickel-plated brass PA-reinforced High alloy steel, non-corrosive |
| Operating status display | Yellow LED |
| Operating reserve display | LED orange |
| Ambient temperature with flexible cable installation | -20 ... 85 °C |
| Protection class | IP65 IP68 IP69K |