

SIMATIC DP, Electronics module f. ET200SP, F-RQ 1x 24 V DC/24..230VAC/5A ST, 20 mm overall width, 1 relay output (2 NO) Summation output current 5 A, load voltage 24 V DC and 24.. 230 V AC, Can be used up to PL E (ISO 13849-1: 2008)/ SIL 3 (IEC 61508: 2010) if control takes place by (e.g. 6ES7136-6DB00-0CA0) F-DQ



General information	
Product type designation	F-RQ 1x24 V DC/24 ... 230 V AC/5 A
usable BaseUnits	BU type F0, BU20-P8+A4+0B
Color code for module-specific color identification plate	CC42
Product function	
• I&M data	Yes; I&M0 to I&M3
Engineering with	
• STEP 7 TIA Portal configurable/integrated as of version	V13
• STEP 7 configurable/integrated as of version	V5.5 SP4 and higher
Supply voltage	
Rated value (DC)	24 V; Coil voltage
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Power	
Power available from the backplane bus	100 mW
Power loss	

Power loss, typ.	1 W
Address area	
Address space per module	
• Inputs	1 byte
Digital outputs	
Number of digital outputs	1
Limitation of inductive shutdown voltage to	No
Controlling a digital input	Yes
Switching capacity of the outputs	
• with resistive load, max.	5 A
• on lamp load, max.	25 W
Switching frequency	
• with resistive load, max.	2 Hz
• with inductive load, max.	0.1 Hz; See data in manual
• with inductive load (acc. to IEC 60947-5-1, DC13), max.	0.1 Hz
• with inductive load (acc. to IEC 60947-5-1, AC15), max.	2 Hz
Total current of the outputs (per module)	
horizontal installation	
— up to 40 °C, max.	5 A; Note derating data in the manual
— up to 50 °C, max.	4 A; Note derating data in the manual
— up to 60 °C, max.	3 A; Note derating data in the manual
vertical installation	
— up to 50 °C, max.	3 A; Note derating data in the manual
Relay outputs	
• Number of relay outputs	1; 2 NO contacts
• Rated supply voltage of relay coil L+ (DC)	24 V
• Current consumption of relays (coil current of all relays), max.	70 mA
• external protection for relay outputs	yes; 6 A, see data in manual
• Relay approved acc. to UL 508	Yes; Pilot Duty B300, R300
Switching capacity of contacts	
— with inductive load, max.	see additional description in the manual
— with resistive load, max.	see additional description in the manual
— Thermal continuous current, max.	5 A
— Switching current, min.	1 mA
— Switching current after exceeding 300 mA, min.	10 mA
— Switching current after exceeding 300 mA, max.	5 A
— Rated switching voltage (DC)	24 V

— Rated switching voltage (AC)	230 V
Cable length	
• shielded, max.	500 m; for load contacts
• unshielded, max.	300 m; for load contacts
• Control cable (input), max.	10 m
Interrupts/diagnostics/status information	
Diagnostics function	yes, firmware update
Diagnostics indication LED	
• RUN LED	Yes; green/red DIAG LED
• Channel status display	Yes; Green LED
Potential separation	
Potential separation channels	
• between the channels	Yes; for SELV / PELV only
• between the channels and backplane bus	Yes
• between the channels and the power supply of the electronics	Yes
Permissible potential difference	
between channels and backplane bus/supply voltage	250 V AC (reinforced insulation)
between backplane bus and supply voltage	75 V DC/60 V AC
Isolation	
Isolation tested with	2 545 V DC/2 s (routine test)
Overvoltage category	III
tested with	
• between channels and backplane bus/supply voltage	DC 2545 V 2 s (routine test), impulse voltage test DC 7200 V / 5 positive and 5 negative pulses (type test)
• between backplane bus and supply voltage	707 V DC (type test)
Dimensions	
Width	20 mm
Weights	
Weight, approx.	56 g
last modified:	01/29/2018