

SIMATIC S7-1500, Digital input module DI 16x24 V DC HF, 16 channels in groups of 16; Input delay 0.05..20 ms; Input type 3 (IEC 61131); diagnostics; Hardware interrupts



General information	
Product type designation	DI 16x24VDC HF
HW functional status	FS01
Firmware version	V2.1.0
<ul style="list-style-type: none"> <li>FW update possible</li> </ul>	Yes
Product function	
<ul style="list-style-type: none"> <li>I&amp;M data</li> </ul>	Yes; I&M0 to I&M3
Engineering with	
<ul style="list-style-type: none"> <li>STEP 7 TIA Portal configurable/integrated as of version</li> </ul>	V13 SP1 / -
<ul style="list-style-type: none"> <li>STEP 7 configurable/integrated as of version</li> </ul>	V5.5 SP3 / -
<ul style="list-style-type: none"> <li>PROFIBUS as of GSD version/GSD revision</li> </ul>	V1.0 / V5.1
<ul style="list-style-type: none"> <li>PROFINET as of GSD version/GSD revision</li> </ul>	V2.3 / -
Operating mode	
<ul style="list-style-type: none"> <li>DI</li> </ul>	Yes
<ul style="list-style-type: none"> <li>Counter</li> </ul>	Yes
<ul style="list-style-type: none"> <li>Oversampling</li> </ul>	No
<ul style="list-style-type: none"> <li>MSI</li> </ul>	Yes

Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	20 mA; with 24 V DC supply
Power	
Power available from the backplane bus	1.1 W
Power loss	
Power loss, typ.	2.6 W
Digital inputs	
Number of digital inputs	16
Digital inputs, parameterizable	Yes
Source/sink input	P-reading
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Digital input functions, parameterizable	
<ul style="list-style-type: none"> <li>• Gate start/stop</li> <li>• Freely usable digital input</li> <li>• Counter <ul style="list-style-type: none"> <li>— Number, max.</li> <li>— Counting frequency, max.</li> <li>— Counting width</li> <li>— Counting direction up/down</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>Yes</li> <li>Yes</li> <li>2</li> <li>1 kHz</li> <li>32 bit</li> <li>Up</li> </ul>
Input voltage	
<ul style="list-style-type: none"> <li>• Type of input voltage</li> <li>• Rated value (DC)</li> <li>• for signal "0"</li> <li>• for signal "1"</li> </ul>	<ul style="list-style-type: none"> <li>DC</li> <li>24 V</li> <li>-30 to +5V</li> <li>+11 to +30V</li> </ul>
Input current	
<ul style="list-style-type: none"> <li>• for signal "1", typ.</li> </ul>	2.5 mA
Input delay (for rated value of input voltage)	
for standard inputs	
<ul style="list-style-type: none"> <li>— parameterizable</li> <li>— at "0" to "1", min.</li> <li>— at "0" to "1", max.</li> <li>— at "1" to "0", min.</li> <li>— at "1" to "0", max.</li> </ul>	<ul style="list-style-type: none"> <li>Yes; 0.05 / 0.1 / 0.4 / 1.6 / 3.2 / 12.8 / 20 ms</li> <li>0.05 ms</li> <li>20 ms</li> <li>0.05 ms</li> <li>20 ms</li> </ul>
for interrupt inputs	
<ul style="list-style-type: none"> <li>— parameterizable</li> </ul>	Yes

for counter/technological functions	
— parameterizable	Yes
<b>Cable length</b>	
• shielded, max.	1 000 m
• unshielded, max.	600 m
<b>Encoder</b>	
Connectable encoders	
• 2-wire sensor	Yes
— permissible quiescent current (2-wire sensor), max.	1.5 mA
<b>Isochronous mode</b>	
Isochronous operation (application synchronized up to terminal)	Yes
Filtering and processing time (TCI), min.	80 µs; At 50 µs filter time
Bus cycle time (TDP), min.	250 µs
<b>Interrupts/diagnostics/status information</b>	
Diagnostics function	Yes
<b>Alarms</b>	
• Diagnostic alarm	Yes
• Hardware interrupt	Yes
<b>Diagnostic messages</b>	
• Monitoring the supply voltage	Yes
• Wire-break	Yes; to I < 350 µA
• Short-circuit	No
<b>Diagnostics indication LED</b>	
• RUN LED	Yes; Green LED
• ERROR LED	Yes; Red LED
• Monitoring of the supply voltage (PWR-LED)	Yes; Green LED
• Channel status display	Yes; Green LED
• for channel diagnostics	Yes; Red LED
• for module diagnostics	Yes; Red LED
<b>Potential separation</b>	
Potential separation channels	
• between the channels	No
• between the channels, in groups of	16
• between the channels and backplane bus	Yes
• between the channels and the power supply of the electronics	No
<b>Isolation</b>	
Isolation tested with	707 V DC (type test)

### Ambient conditions

#### Ambient temperature during operation

- horizontal installation, min. 0 °C
- horizontal installation, max. 60 °C
- vertical installation, min. 0 °C
- vertical installation, max. 40 °C

### Decentralized operation

Prioritized startup Yes

### Dimensions

Width 35 mm

Height 147 mm

Depth 129 mm

### Weights

Weight, approx. 240 g

**last modified:** 01/29/2018