

# PANEL MOUNT INDICATOR, RECTANGULAR

## NEON AND INCANDESCENT TECHNOLOGY

MOUNTING CUT-OUT, 0.375" x 1.28"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
<b>INCANDESCENT 12V SERIES</b>				
WL-1020Q2D1	RED	12V-14V	80mA	25,000
WL-1020Q2D3	AMBER	12V-14V	80mA	25,000
WL-1020Q2D5	GREEN	12V-14V	80mA	25,000
<b>INCANDESCENT 28V SERIES</b>				
WL-1021Q2D1	RED	24V-28V	40mA	25,000
WL-1021Q2D3	AMBER	24V-28V	40mA	25,000
WL-1021Q2D5	GREEN	24V-28V	40mA	25,000
<b>NEON 115VAC SERIES</b>				
WL-1022Q2D1	RED	105-125VAC	1.5mA	25,000
WL-1022Q2D3	AMBER	105-125VAC	1.5mA	25,000
WL-1022Q2D5	GREEN	105-125VAC	1.5mA	25,000
<b>NEON 230VAC SERIES</b>				
WL-1023Q2D1	RED	208-250VAC	1.5mA	25,000
WL-1023Q2D3	AMBER	208-250VAC	1.5mA	25,000
WL-1023Q2D5	GREEN	208-250VAC	1.5mA	25,000

### NOTES


1. Recommended panel thickness  
0.030" to 0.100"
2. .250" terminals are standard
3. Storage temperature  
TSTG: -25°C - +80°C
4. Ambient temperature  
TA: -20°C - +60°C
5. AC operation only for neon type
6. AC/DC operation for incandescent type
7. Voltage tolerance  
VOP: ±10%
8. Body Material  
Nylon, black
9. Lens Material  
Polycarbonate
10. .187" terminals available upon request
11. 6" lead wires available upon request

### CERTIFICATIONS

UL (E340667), RoHS



### DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches



### OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

**wamco**  
LIGHTING