


HD-TVI 2MP Intensifier® T Traditional Camera

HTINTT5T Accepts C & CS auto iris & manual type lenses, dark gray housing



lens not included



Features

- Full HD resolution over coax (HD-TVI)
- See color in almost complete darkness without IR LEDs
- Supports Full HD 1080p @ 30fps
- No problems caused by objects that reflect or absorb IR light sources
- True WDR operation
- With presets for different scenarios
- Full OSD operation via UTC (TVI output only)
- Additional analog output for 960H
- 12VDC / 24VAC dual voltage operation
- 5 year warranty

Specifications

Image Sensor 1/3" Progressive Scan CMOS, 2MP
 Resolution 1080p
 Minimum Illumination 0.001 lux
 Effective Pixels 1984 (H) x 1105 (V)
 Total Pixels 2000 (H) x 1121 (V)
 TV System NTSC
 Scanning Frequency 15.734kHz (H) / 59.94Hz (V)
 Scanning System Progressive
 Synchronization Internal
 Communication UTC
 S/N Ratio more than 50dB
 Video Output CVBS: 1.0Vp-p / 75 ohms
 Electronic Shutter Speed Auto / Manual
 OSD Available
 DWDR On / Off (level adjustable)
 Backlight Compensation BLC / HLC / Off
 Day/Night Color / BW / Auto / Ext

AGC Level adjustable
 White Balance ATW / Push / Manual
 Intensify Auto / Off (selectable x2 - x512)
 Motion Detection On / Off (4 programmable zones)
 Privacy Masking On / Off (8 programmable zones)
 Speco DNR High / Med / Low / Off
 Sharpness On / Off (level adjustable)
 Mirror On / Off
 Power Consumption 12VDC, 150mA / 24VAC, 2W
 Power Supply 12VDC / 24VAC dual voltage operation
 (power supply not included)
 Operating Temperature 14° F – 122° F
 Storage Temperature -4° F – 140° F
 Dimensions 2.5" (W) x 2.2" (H) x 3.46" (L)
 Weight 1.5 lbs.

Optional Accessories



PSW4
24VAC
Power Supply



PSW5
12VDC
Power Supply



VCH401HBMT
Housing with Heater,
Blower & Bracket



TVIUTPPT
HD Video
Transceiver with
Pigtail (Balun)



TVIUIPT
HD Video
Transceiver

Optional Lenses

VFMP2.712DC 2.7-12mm megapixel varifocal lens