

# **Surface Mount Microprocessor Crystal 2.0 x 1.6**

#### **Features**

- Compact Design
- High Accuracy
- Excellent for High Density Surface Mounting



# Specifications

Paran	neter	Value		
Frequency Range		10.000 to 45.000 MHz		
Mode of Oscillation	Fundamental	10.000 to 45.000 MHz		
Frequency Tolerance	e at 25°C	$\pm 100$ ppm Standard ( $\pm 10$ , $\pm 30$ & $\pm 50$ ppm available)		
Frequency Stability	over Temperature	$\pm 100$ ppm Standard ( $\pm 10$ , $\pm 30$ & $\pm 50$ ppm available)		
Operating Temperat	ture Range	-20°C to +70°C Standard -40°C to +85°C Extended		
Storage Temperatur	e Range	-40°C to +85°C		
Aging		±3 ppm per Year maximum		
Load Capacitance		16 pF to 32 pF or Series		
Equivalent Series Re	sistance	See Table 1		
Shunt Capacitance		7.0 pF maximum		
Drive Level		100 μW Typ., 500 μW Max		
Shock Resistance		±5 ppm Maximum 75 cm Drop Test in 3 axes onto a hardwood surface		

#### Table 1


Frequency (MHz)	Mode	MAX ESR (Ohms)
10.000 to 11.999	FUND	150
12.000 to 15.999	FUND	100
16.000 to 29.999	FUND	70
30.000 to 45.000	FUND	50

## Environmental


Parameter	Value
Moisture Sensitivity Level	1
RoHS	6/6 Complaint & Lead Free
REACH SVHC	Compliant
Halogen Free	Compliant
ESD Classification Level	N/A
Termination Finish	Au
Unit Weight (grams)	0.019



## **Mechanical Specification**



## Carrier Tape Dimension



**NOTE: REFER TO EIA-481 FOR DIMENSIONS** 

#### Packaging

178 mm Reel Diameter 8 mm Tape Width, 4 mm Pitch Quantity: 3000 pcs per Reel

In accordance with EIA-481

## Part Numbering

1 41 4 1 4 4 1 4 4 4 4 4 4 4 4 4 4 4 4						
JD	-	24.000	-	18	-	XXXX
Product Family	The second secon	Frequency (MHz)	-	Load Capacitance (pF)  16 to 32 pF or S for Series	-	1) Tolerance, 2) Stability, 3) Mode, 4) Temperature  Tolerance:  E=±10 ppm, H=±15 ppm D=±20ppm, A=±25 ppm, F=±30 ppm, B=±50 ppm, C=±100 ppm (std)  Stability:  E=±10 ppm, H=±15 ppm, D=±20ppm, A=±25 PPM, F=±30 ppm, B=±50 ppm, C=±100 ppm (std)  Mode: blank = Fundamental, 3=3 <sup>rd</sup> Overtone
						Temperature range: blank standard, E=Extended

#### **EXAMPLE: JD-24.000-12-BB**


Surface Mount Microprocessor Crystal, 2.0 X 1.6 mm, 24.000 MHz, 18 pF load Capacitance, standard tolerance (±50 ppm) and stability (±50 ppm), Fundamental mode, standard Temperature range -20°C to +70°C

#### EXAMPLE: JD-8.000-10-DBE

Surface Mount Microprocessor Crystal, 2.0 X 1.6 mm, 8.000 MHz, 10 pF load Capacitance, tolerance (±20 ppm), stability (±50 ppm), Fundamental mode, Extended Temperature range -40°C to +85°C



### **Reflow Profile**



Reflow Profile (Reference IPC/JEDEC J-STD-020)			
Temperature Min Preheat	T <sub>SMIN</sub>	150°C	
Temperature Max Preheat	T <sub>SMAX</sub>	200°C	
Time (T <sub>SMIN</sub> to T <sub>SMAX</sub> )	t <sub>S</sub>	60 – 180 sec.	
Temperature	TL	217°C	
Peak Temperature	T <sub>P</sub>	260°C	
Ramp-Up Rate	R <sub>UP</sub>	3°C / sec. max	
Ramp-Down Rate	R <sub>DOWN</sub>	6°C / sec. max	
Time within 5°C of Peak	T <sub>P</sub>	10 sec.	
Temperature			
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec.	
Time	TL	60 – 150 sec.	



#### MARKING

RFF.FF xxLyw

FF.FF – Frequency in MHz x – Internal Production ID code

L - Load Capacitance Code

y – Year code

w – Week code

LOAD CAPACITANCE CODE				
CODE	C <sub>L</sub> (pF)	CODE	C <sub>L</sub> (pF)	
Α	20	J	12	
В	18	K	10	
С	16	М	14	
D	30	N	15	
F	12.5	Р	13	
G	32	8	8	
Н	22	9	9	

YEAR CODE		
Year	Code	
2011	1	
2012	2	
2013	3	
2014	4	
2015	5	
2016	6	
2017	7	
2018	8	
2019	9	
2020	0	

ALPHA WEEK CODE					
Week	Code	Week	Code	Week	Code
1	а	19	S	37	K
2	b	20	t	38	L
3	С	21	u	39	M
4	d	22	V	40	Ν
5	е	23	W	41	0
6	f	24	Х	42	Р
7	g	25	у	43	Q
8	h	26	Z	44	R
9	i	27	Α	45	S
10	j	28	В	46	Т
11	k	29	С	47	U
12		30	D	48	V
13	m	31	Е	49	W
14	n	32	F	50	Χ
15	0	33	G	51	Υ
16	р	34	Н	52	Z
17	q	35			
18	r	36	J		·

#### APPROVAL

DRAWN BY	FP, 28 March 2017
APPROVED BY	FP, 28 March 2017
REVISION	A, Initial Release