



Activated carbon filter LFX-1/4-D-MINI

Part number: 532802
Classic



High performance filter for virtually oil-free, odorless compressed air, suitable for use in the food processing industry

Modern alternatives can be found by entering the first four characters of the type code in the search field.



Data sheet

Feature	Value
Size	Mini
Series	D
Assembly position	Vertical +/- 5°
Design structure	Active carbon filter Fiber filter
Bowl guard	Metal bowl guard
Working pressure	0 ... 16 bar
Recommended maximum standard flow rate	360 l/min
Max. standard flow rate for air quality class	360 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [1:4:2] Inert gases
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Storage temperature	-10 ... 60 °C
Air purity class at output	Compressed air to ISO 8573-1:2010 [1:4:1] Inert gases
Medium temperature	5 ... 30 °C
Residual oil content	<= 0.003 mg/m ³
Ambient temperature	-10 ... 60 °C
Product weight	376 g
Mounting type	Optional Line installation With mounting bracket
Pneumatic connection	G1/4
Pneumatic connection, port 1	Subbase G1/4
Pneumatic connection, port 2	Subbase G1/4
Materials note	Free of copper and PTFE Conforms to RoHS
Material filter	Active carbon Mesh
Material housing	Zinc die-casting
Material bowl	PC