

## Surge protection plug - TC EXTENDER PT-IQ-2S - 2702258

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Replaceable surge protection module, only for Ethernet extender TC EXTENDER 6004 ETH-2S (2702255), 2 SHDSL ports, two-wire protection for floating SHDSL cables, two-level protective circuit



### Key Commercial Data

Packing unit	1 STK
Weight per Piece (excluding packing)	120.000 g
Custom tariff number	85363090
Country of origin	Germany

### Technical data

#### Dimensions

Width	22 mm
Height	96 mm
Depth	80 mm

#### Ambient conditions

Degree of protection	IP20
----------------------	------

#### General

Net weight	48.68 g
------------	---------

#### Standards and Regulations

Standards/regulations	IEC 61643-21
	IEC 60664-1
IEC test classification	B1
	C1
	C2

# Surge protection plug - TC EXTENDER PT-IQ-2S - 2702258

## Technical data

### Standards and Regulations


	C3
	D1
Noxious gas test	ISA-S71.04-1985 G3 Harsh Group A

### Environmental Product Compliance


China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings

Schematic diagram



Schematic diagram



Replacement of protective module

## Classifications

### eCl@ss

eCl@ss 5.1	27242208
eCl@ss 6.0	27242208
eCl@ss 8.0	27130807
eCl@ss 9.0	27130807

### ETIM

ETIM 2.0	EC000943
ETIM 3.0	EC000943
ETIM 4.0	EC000943
ETIM 5.0	EC000943
ETIM 6.0	EC000943

### UNSPSC

UNSPSC 6.01	30212010
-------------	----------

## Surge protection plug - TC EXTENDER PT-IQ-2S - 2702258

### Classifications

#### UNSPSC

UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

### Accessories

#### Necessary add-on products

#### Modem - TC EXTENDER 6004 ETH-2S - 2702255



Managed Ethernet extender, point-to-point, line and ring structures, data rates up to 30 Mbps, distances of up to 20 km on in-house copper cables, replaceable surge protection, 2 SHDSL ports, 4-port switch, diagnostics via display and Ethernet