

Condensate drain WA-1-B

Part number: 158497

FESTO



Data sheet

Feature	Value
Type of actuation	mechanical
Assembly position	vertical +/- 10°
Manual override	Pushing
Condensate drain	fully automatic
Design structure	External, mechanical, fully automated
Measured variable	Fill-level
Valve function	2/2 closed, monostable
Working pressure	4 ... 16 bar
Operating medium	Water
Storage temperature	-20 ... 60 °C
Medium temperature	0 ... 60 °C
Ambient temperature	0 ... 60 °C
Product weight	210 g
Mounting type	Line installation
Condensate drain connection	G1/4
Pneumatic connection	M9
Material housing	Brass PA