



Electro-cylinder ESBF-LS-32-300-2.5P

Part number: 8022571

FESTO



Data sheet

| Feature | Value |
|--|---|
| Working stroke | 300 mm |
| Size | 32 |
| Stroke | 300 mm |
| Piston rod thread | M10x1,25 |
| Reversing backlash | 100 µm |
| Spindle diameter | 12 mm |
| Spindle pitch | 2.5 mm/U |
| Max. angular deflection of piston rod +/- | 0.25 deg |
| Based on the standard | ISO 15552 |
| Assembly position | Any |
| Piston-rod end | Male thread |
| Motor type | Stepper motor Servomotor |
| Position detection | For proximity sensor |
| Design structure | Electro-cylinder with lead screw |
| Spindle type | Plain thread |
| Protection against torque/guide | with plain-bearing guide |
| Max. acceleration | 2.5 m/s ² |
| Max. speed | 0.125 m/s |
| Repetition accuracy | ±0,05 mm |
| Duty cycle | 100% |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| Storage temperature | -20 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Protection class | IP40 |
| Ambient temperature | 0 ... 60 °C |
| Max. drive torque | 1.1 Nm |
| Max. radial force at drive shaft | 115 N |
| Max. feed force Fx | 1,000 N |
| No-load driving torque | 0.1 Nm |
| Mass moment of inertia JH per meter of stroke | 1.6373 kgcm ² |
| Mass moment of inertia JL per kg of working load | 0.0016 kgcm ² |
| Mass moment of inertia, JO | 0.0164 kgcm ² |
| Moving mass with 0 mm stroke | 198 g |
| Additional weight per 10 mm stroke | 34 g |
| Basic weight for 0 mm stroke | 667 g |
| Additional mass factor per 10 mm of stroke | 9 g |
| Mounting type | with internal (female) thread or accessories |
| Interface code, actuator | D32 |
| Materials note | Contains PWIS substances Conforms to RoHS |
| Material cover | Wrought Aluminum alloy Smooth anodized |

| Feature | Value |
|--------------------------|---|
| Material piston rod | High alloy steel, non-corrosive |
| Material screws | Steel Galvanized |
| Material spindle nut | Roller bearing steel |
| Material spindle | Roller bearing steel |
| Material cylinder barrel | Wrought Aluminum alloy Smooth anodized |