

# Crimp splice protection - FOC-CRIMPSPLICE-PROTECT - 1019678

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp splice protection, type: Straight, degree of protection: IP20, connection method: Crimp, cable outlet: above and below, color: Bare metallic

## Product Description

Crimp splice protection in blister packaging

### Why buy this product

- No attenuating effects on the fusion splice
- Mechanical protection for fusion splices
- Telekom TS 0338/96 approval

## Key Commercial Data

Packing unit	12 STK
Minimum order quantity	12 STK
GTIN	
GTIN	4055626701189

## Technical data

### Mechanical characteristics

Fiber	GOF
Connection method	Crimp
External cable diameter	250 µm (Includes primary coating)
Cable outlet	above and below
Color	Bare metallic
Mounting type	Crimp splice protection
Degree of protection	IP20
Type	Straight
Type of note	Order information:
Note	Splice protection for FDX 20 splice boxes

## Crimp splice protection - FOC-CRIMPSPLICE-PROTECT - 1019678

### Technical data

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (according to DIN EN 61300-2)
Degree of protection	IP20

#### Material data

Material	Metal
Depth	1.2 mm
Height	3 mm
Fiber	GOF

#### Line characteristics

Cable type	Fiberglass
------------	------------

---

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>