

Motor controller CMMP-AS-C2-3A-M0

Part number: 1622901

FESTO



Data sheet

Feature	Value
Mounting type	On subbase Tightened
Product weight	2,100 g
Display	Seven-segment display
CE symbol (see declaration of conformity)	according to EU-EMV guideline according to EU machines guideline according to EU low voltage guideline
Authorization	RCM Mark c UL us - Listed (OL)
Storage temperature	-25 ... 70 °C
Ambient temperature	0 ... 40 °C
Relative air humidity	0 - 90 %
Protection class	IP10 IP20
Degree of contamination	2
Materials note	Contains PWIS substances Conforms to RoHS
Nominal operating voltage, phases	Single-phase
Nominal operating voltage, AC	230 V
Permissible voltage fluctuation	+/- 10 %
Line frequency	50 ... 60 Hz
Nominal current	2 ... 3 A
Active PFC	Yes
Mains filter	Integrated
Max. intermediate circuit voltage, DC	320 V
Braking resistance	60 Ohm
Braking resistance pulse power	2.8 kVA
Nominal DC voltage, logic power supply	24 V
Permissible range, logic voltage	± 20 %
Current consumption, logic power supply without clamping brake	0.55 A
Output voltage range AC	3x 0 - 270 V
Nominal output current	2.5 A
Effective nominal current per phase	2.5 A
Effective peak current per phase	5 A
Max. peak current duration	5 s
Nominal controller power	500 VA
Peak power	1,000 VA
Output frequency	0 ... 1,000 Hz
Parameters configuring interface	Parameters configuration and commissioning USB Ethernet
Fieldbus coupling	CANopen Modbus/TCP
Communications profile	DS301/DSP402
Process interface	I/O coupling For 256 position sets

Feature	Value
Max. fieldbus transmission speed	1 Mbit/s
Bus connection	9-pin Sub-D Plug socket
Encoder interface output, characteristics	Resolution 16384 ppr
Encoder interface output, function	Actual value feedback via encoder signals in speed control mode Set point specification for downstream slave drive unit
Encoder interface input, characteristics	3-phase encoding signals EnDat HIPERFACE RS422 SINCOS
Encoder interface input, function	Encoder signal, speed set point in RPM In synchronous operation as specified speed in RPM for the slave drive unit
Number of digital logic inputs	10
Logic input characteristics	Electrically isolated Freely configurable
Logic input working range	8 ... 30 V
Number of 24 V DC digital logic outputs	5
Digital logic output characteristics	Electrically isolated Freely configurable to a given extent
Max. current, digital logic outputs	100 mA
Number of analog set point inputs	2
Set point input characteristics	Differential inputs Can be configured for speed in RPM Can be configured for current
Set point input working range	± 10 V
Set point input impedance	20 kOhm
Number of analog monitor outputs	2
Monitor output working range	± 10 V
Monitor output resolution	9 Bit
Monitor output characteristics	Short circuit proof
Safety function	Safe torque off (STO) Safe stop 1 (SS1)
Safety Integrity Level (SIL)	Safe torque off (STO)/SIL 3/SILCL 3
Performance level (PL)	Safe Torque off (STO)/Category 4, Performance Level e
Diagnostic coverage	97 %
SFF Safe Failure Fraction	99.17 %
Hardware fault tolerance	1
Proof test interval	20 a
Certificate issuing department	TÜV Rheinland