

## Cat5e 350 MHz Molded Shielded STP Patch Cable (RJ45 M/M), Blue, 15 ft.

MODEL NUMBER: **N105-015-BL**



### Highlights

- Rated for 350 MHz/1 Gbps communications
- Molded RJ45 male connectors with gold-plated contacts
- Protects Ethernet networks against EMI/RFI line noise
- 4-pair 24 AWG stranded STP with drain wire
- TIA/EIA and UL certified

### Package Includes

- N105-015-BL Cat5e 350 MHz Molded Shielded STP Patch Cable (RJ45 M/M), Blue, 15 ft.

### Description

The N105-015-BL Cat5e 350 MHz Molded Shielded STP Patch Cable is recommended for connecting network components like printers, computers, copiers, routers, servers, modems, hubs, patch panels and switches in high-density data centers. Designed for fast transmission and excellent signal quality, this 15-foot blue cable ensures peak performance throughout your local area network (LAN). EMI/RFI shielding protects your Ethernet network from disruptive line noise.

Manufactured from 24 AWG copper wire and a durable PVC jacket, the four-pair stranded STP N105-015-BL delivers speeds up to 350 MHz/1 Gbps. Molded RJ45 male connectors with gold-plated contacts guarantee an accurate signal transfer. Integral strain relief ensures the cable and connectors last a long time. Certified to TIA/EIA-568B and UL standards.

### Features

Recommended Solution for Your Networking Needs

- Ideal for connecting components like printers, computers, copiers, routers, servers, modems and switches in high-density data centers
- Designed for fast transmission and excellent signal quality
- Ensures peak performance throughout your LAN
- EMI/RFI shielding protects network from disruptive line noise
- Delivers speeds up to 350 MHz/1 Gbps

Premium Construction for Superior Performance

- Made from 24 AWG copper wire
- PVC 4-pair stranded STP with drain wire



- Molded RJ45 male connectors with gold-plated contacts
- Integral strain relief for long life
- TIA/EIA and UL certified

## Specifications

MODEL TEXT	
Key Benefit	Connects network components like printers, computers, copiers, routers, servers, modems, hubs, patch panels and switches. Recommended for high-density data centers and fast Ethernet networks.
INPUT	
Cable Length (ft.)	15
Cable Length (m)	4.6
PHYSICAL	
Color	Blue
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>