


## CAPACITANCE LEVEL SWITCH

For Solids, Liquids or Slurries, Fail-Safe Protection, <1 pF Sensitivity





The **MODEL CLS1** Capacitance Level Switches provides reliable point level measurement of solids, liquids and slurries in metallic or non-metallic tanks and vessels. It detects the presence or absence of material in contact with the probe by sensing a change in the capacitance.

## FEATURES/BENEFITS

- Electronics provide highly sensitive measurement detection (requires less than a 1 picofarad shift from ambient)
- State of the art technology ignores material build-up on the vessel sidewall or along the probe assembly
- One time calibration is simple with a single multi-turn potentiometer
- · Red LED on housing indicates sensor status
- Adjustable 1-30 second time delay and a 5 A, SPDT fail-safe relay output
- Added installation flexibility with vertically or horizontally mounting

## **APPLICATIONS**

- High or low level detection
- Bins
- SilosTanks
- Hoppers
- Chutes

## **SPECIFICATIONS**

**Service:** Solids, liquids, or slurries. **Wetted Material:** CPVC.

**Temperature Limits:** Process: -40 to 240°F (-40 to 116°C); Ambient: -40 to 185°F (-40 to 85°C).

**Enclosure Rating:** NEMA 4X (IP66), PVC. dust tight, water resistant.

Switch Type: SPDT.

Electrical Rating: 5 A @ 250 VAC.

Power Requirements: 120 VAC, 1.5 VA. Conduit Connection: 3/4" female NPT. Process Connection: 1" male NPS. Mounting Orientation: Vertical or horizontal.

Sensitivity: Adjustable to < 1 pF.
Fail-Safe: Switch selectable, high/low.
Time Delay: Adjustable 1 to 30 s.

Weight: 2.0 lb (0.91 kg).

MODEL CHART	
Model	Description
CLS1	Capacitance level switch