

Heavy-Duty Power Extension Cord, 15A, 14 AWG (IEC-320-C14 to IEC-320-C13), Green, 6 ft.

MODEL NUMBER: P005-006-AGN



Description

The P005-006-AGN Heavy-Duty Power Extension Cord is recommended for replacing a lost or worn-out power cord or extending your current power connection by six feet. It features a green SJT jacket and fully molded green ends, allowing you to easily identify your connections in a crowded workstation. A C14 male connector on one end and a C13 female connector on the other let you attach computers, printers, scanners, power supplies, monitors and other compatible hardware. This six-foot 15A cord supports voltages up to 250V. It's UL-listed and features a flexible SJT jacket and 14 AWG wire for easy routing through tight areas.

Features

Safe, Reliable Power Solution

- Connects hardware with C13/C14 power connectors
- Ideal for replacing an old or lost cord
- Extends current power connection by 6 ft.

Color-Coded Cable and Connectors

- Colored green for easy identification in crowded rack or workstation

Optimum Construction

- 14 AWG wire
- Flexible SJT jacket
- 250V/15A rating
- UL-listed

Highlights

- Easy-to-identify green SJT jacket and fully molded green ends
- Flexible 14 AWG wire for easy routing
- 250V/15A rating
- UL-listed
- Also recommended for replacing lost or old power cord

Package Includes

- P005-006-AGN Heavy-Duty Power Extension Cord, Green, 6 ft.



Specifications

| MODEL TEXT | |
|-------------------------------------|---|
| Key Benefit | Color-coded cable connects hardware, such as computers, printers, scanners, power supplies and monitors, with C13/C14 power connectors. Or extends your current power connection by 6 ft. |
| INPUT | |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.8 |
| Cable Length (in.) | 72 |
| Cable Length (cm) | 182.88 |
| PHYSICAL | |
| Color | Green |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4 F TO 140 F (-20 C TO 60 C) |
| Storage Temperature Range | -4 F TO 140 F (-20 C TO 60 C) |
| Operating Humidity Range | 10-85% RH |
| Storage Humidity Range | 10-85% RH |
| CONNECTIONS | |
| Side A - Connector 1 | IEC-320-C14 |
| Side B - Connector 1 | IEC-320-C13 |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>