

LED machine light - PLD M 260 W-40/80 190/D40 - 2702938

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



LED machine light, 24 V DC, emission angle 40 °/80 °, color temperature 5000 K, length 190 mm, diameter 40 mm, M12 connector, Light housing: Anodized aluminum, Pane: Single-pane safety glass (ESG, thermally toughened float glass), pivoting, resistant to coolants and lubricants

Product Description

This LED machine light is designed to provide illumination inside or on machinery. You can use the light in harsh environments.

This is possible thanks to:

- The high degree of protection
- Resistance to common cooling agents and lubricants
- Resistance to vibrations and shock
- The 4 mm thick safety glass

The small diameter of just 40 mm enables mounting even where space is at a premium.

Mounting is by means of holders or brackets (neither of which are supplied as standard) in which the light can swivel and the lighting can therefore be optimally aligned.

Your advantages

- ✔ Space saving, thanks to the small diameter
- ✔ Plug-in supply line enables free choice of the cable length as well as quick and easy installation
- ✔ Focused illumination, thanks to swivel action
- ✔ IP67 protection and resistance to cooling agents and lubricants enables use in machine tools
- ✔ Can be used at high temperatures and can be subjected to strong vibrations and shocks
- ✔ Safety glass enables use even in environments with potential mechanical strain
- ✔ ETL approval permits use on the North American market
- ✔ Particularly economical thanks to energy-efficient LED technology and an LED service life of at least 60,000 h

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4055626443911

Technical data

Dimensions

Width	40 mm
Height	30 mm
Length	190 mm
Note on dimensions	Length without M12 flush-type connector

LED machine light - PLD M 260 W-40/80 190/D40 - 2702938

Technical data

Ambient conditions

Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 75 °C
Permissible humidity (operation)	95 %
Permissible humidity (storage/transport)	95 % (non-condensing)
Air pressure (operation)	69 kPa ... 102 kPa
Air pressure (storage/transport)	69 kPa ... 102 kPa
Degree of protection	IP67

General

Note	The PLD M-ME MC/D40 mounting holder (Order No. 2702491) or the PLD M-ME MB/D40 mounting bracket (Order No. 2702527) is required in order to mount the light.
Net weight	460 g
Mounting type	Screw mounting
Assembly instructions	Mounting with mounting holders or mounting brackets, please observe the notes in the package slip.

Power supply for module electronics

Connection method	M12 connector, (A-coded)
Number of positions	4
Permissible conductor cross section	min. 0.34 mm ²
Supply voltage	24 V DC
Supply voltage range	20 V DC ... 28 V DC
Current consumption	typ. 0.21 A (at 24 V DC)
Power consumption	approx. 5 W (at 24 V DC)
Type of protection	Surge protection
	Reverse polarity protection

Connection data

Connection method	M12 connector, (A-coded)
-------------------	--------------------------

Light properties

Source of light type	LED
Number of LEDs	12
Service life, lighting appliance	60000 h (L70)
Light color	Neutral white
Color temperature	5000 K
Color rendering index	80
Luminous flux	approx. 490 lm (Net luminous flux)
Illumination	max. 393 lx (Distance of 1 m)
Average illumination	223 lx (Distance of 1 m over 1 m ² area)
Emission angle	40 ° (C0-C180)

Standards and Regulations

LED machine light - PLD M 260 W-40/80 190/D40 - 2702938


Technical data

Standards and Regulations

Mechanical tests	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6 4g
	Shock in acc. with EN 60068-2-27/IEC 60068-2-27 50g
Protection class	III, IEC 61140, EN 61140, VDE 0140-1

Drawings

Dimensional drawing



Approvals

Approvals

Approvals

ETLus / cETL / cETLus

Ex Approvals

Approval details

ETLus		http://www.intertek.com	LV-Lighting-Systems
-------	--	---	---------------------

cETL		http://www.intertek.com	Luminaires
------	--	---	------------

cETLus		http://www.intertek.com	
--------	--	---	--

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>