

Datasheet

# 600W Enclosed Power Supply Range



## Features:

- High efficiency, long life and high reliability
- 3 Year Warranty
- Universal Input
- Wide Operating Ambient Temperature Range
- Operating Altitude of up to 5000m on many of the range
- UL & CE Approved

The 600W enclosed power supply range has been specially designed to offer high efficiency, long life and high reliability for use in a variety of applications. This range comprises of 4 models with outputs of either 12v, 24v, 36v or 48v. Each model is approved to CE, CB, UL and come with a three year warranty.





**ENGLISH**

RS Stock Code		1618239	1618240	1618241	1618242
Output	DC Voltage	12V	24V	36V	48V
	Rated Current	42A	26.5A	17.5A	13.6A
	Current Range	0~42A	0~26.5A	0~17.5A	0~13.6A
	Ripple & Noise	<180mVp-p	<150mVp-p	<150mVp-p	<200mVp-p
	Voltage Adjustment Range	5%~10% of Rated Output Voltage			
	Voltage Accuracy	+/- 1.0%			
	Line Regulation	+/- 0.5%			
	Load Regulation	+/- 1.0%			
	Overshoot & Undershoot	<5.0%			
	Rise Time	<1.5 Seconds - 230Vac at 100% Load			
	Hold Up Time	>16mS - 230Vac at 100% Load			
Input	Full Input Voltage Range	90~264Vac			
	Full Frequency Range	47-63Hz			
	AC Current	< 9A			
	In Rush Current	<20A@230Vac			
	Leakage Current	Input-Output:<0.25mA    Input-PG:<3.5mA			
Protection	Over Load	110~135% rated output current			
	Short Circuit	Long Term Mode, auto-recovery			
Environment	Working Temp	-30°C ~ +70°C (230Vac) (Refer to output derating curve)			
	Working Humidity	20~90%RH non-condensing			
	Storage Temp	-40°C ~ +85°C			
	Storage Humidity	10 ~ 95%RH non-condensing			
Saftey	Saftey Standards	UL60950-1, EN60950-1: 2006 IEC 60950-1:2005			
	Withstand Voltage	I/P-O/P: 3KVac   I/P-FG: 1.5KVac   O/P-FG: 0.5KVac			
	Isolation Resistance	> 100MOhms			
	EMC Emmission	Compliance to EN55022 Class B			
Others	EMC Immunity	Compliance to EN61000-4-2, 3, 4, 5, 6, 8, 11			
	Lifetime	200,000 Hours (25°C)			
	Size	218mm x 116.5mm x 41mm			
	Package	6pcs/ctn, 8.7KG			
Notes	<p>1)All parameters NOT specially mentioned are measured at 230Vac input, rated load and 25°C of ambient temperature.            2)Measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1 uF &amp; 47uF parallel capacitor.            3)The power supply is considered a component which must be installed into final equipment. The final equipment must be re-confirmed that it meets all applicable directives.</p>				