



ENGLISH

Datasheet

# 150W Enclosed Power Supply Range



## Features:

- No Load Power Consumption <math><0.5\text{W}</math>
- Small Compact Design
- Cooling by free air convection
- High efficiency, long life and high reliability
- 3 Year Warranty
- Universal Input
- Withstand 5G Vibration Test
- UL & CE Approved

The 150W enclosed power supply range has been specially designed to offer high efficiency, long life and high reliability for use in a variety of applications. This range comprises of 4 models with outputs of either 12v, 24v, 36v or 48v. Each model is RoHS, CE, UL approved and come with a three year warranty.





ENGLISH

SPECIFICATION				
RS Stock Code	161-8297	161-8299	161-8300	161-8301
DC Voltage	12V	24V	36V	48V
Rated current	12.5A	6.5A	4.3A	3.3A
Current Range	0~12.5A	0~6.5A	0~4.3A	0~3.3A
Rated Power	150W	156W	155W	158W
Ripple & Noise	150mVp-p	200mVp-p	200mVp-p	200mVp-p
Voltage regulation range	±10.0%			
Voltage Accuracy	≤ 1%			
Line adjustment	≤ 1%			
Load adjustment rate	≤ 1%			
No Load Power Consumption	<0.5W			
Rise	≤ 30ms 100% Rated Load			
Hold up time	30ms/ 100% Rated Load			
Voltage Range	85~132VAC/170~264VAC, Selected by switch			
Frequency	47~63Hz			
Input Current	MAX 2.8/115 Vac 1.6A/230VAC			
Efficiency	88%	89%	89%	90%
Alternating Current	2.8A/115VAC 1.6A/230VAC			
Inrush current	<60A/230VAC			
Leakage Current	<0.75mA/240Vac			
Overload	120 ~ 150% of rated output, auto-recovery			
Short circuit	Hiccup Mode, auto-recovery			
Over Voltage	115%-135% rated output voltage, Shut down o/p voltage, re-power to recover			
Working temp	-30°C ~ +70°C (See derating curve)			
Working humidity	20 ~ 95%RH (Non condensing)			
Storage temp	-40°C ~ +80°C			
Storage humidity	10 ~ 95%RH (Non condensing)			
Temp coefficient	±0.03%/°C (0~50°C)			
Vibration resistance	10~500Hz, 5G, 10min/cycle, X, Y, Z 60min in each direction			
Safety Standard	CE, UL60950-1, EN60950-1			
Withstand Voltage	I/P-O/P:3.0KV AC, I/P-FG:2.0KV AC,O/P-FG:0.5KV AC			
Isolation Resistance	I/P-O/P,I/P-FG,O/P-FG:100MΩ/500VDC/25°C/70%RH			
EMC	EN55022 CLASS B			
Lifetime	380,000 hours(25°C)			
Size	159×97×30 (L*W*H)			
Weight	0.48Kg/pc 44pcs/carton			