

SIMATIC ET 200SP, Digital input module, DI 8x 24V DC Basic, type 2 (IEC 61131), sink input, (PNP, P-reading), Packing unit: 1 piece, fits to BU-type A0, Colour Code CC01, input delay time 0,05..20ms, module diagnostics for: supply voltage



General information	
Product type designation	DI 8x24 VDC BA
Firmware version	V0.0
<ul style="list-style-type: none"> FW update possible 	No
usable BaseUnits	BU type A0
Color code for module-specific color identification plate	CC01
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M3
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated as of version 	V14
<ul style="list-style-type: none"> STEP 7 configurable/integrated as of version 	V5.5 SP3 / -
<ul style="list-style-type: none"> PROFIBUS as of GSD version/GSD revision 	One GSD file each, Revision 3 and 5 and higher
<ul style="list-style-type: none"> PROFINET as of GSD version/GSD revision 	GSDML V2.3
Operating mode	
<ul style="list-style-type: none"> DI 	Yes
<ul style="list-style-type: none"> Counter 	No
<ul style="list-style-type: none"> Oversampling 	No

- MSI

No

Supply voltage

Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes

Input current

Current consumption, max.	70 mA; All channels are supplied from the encoder supply
---------------------------	--

Encoder supply

Number of outputs	8
Output voltage encoder supply, min.	19.2 V
Short-circuit protection	Yes; per module
24 V encoder supply	
<ul style="list-style-type: none"> • 24 V 	Yes
<ul style="list-style-type: none"> • Short-circuit protection 	Yes
<ul style="list-style-type: none"> • Output current per channel, max. 	700 mA
<ul style="list-style-type: none"> • Output current per module, max. 	700 mA

Power loss

Power loss, typ.	1.6 W; 24 V, 8 inputs supplied via encoder supply
------------------	---

Address area

Address space per module	
<ul style="list-style-type: none"> • Inputs 	1 byte

Hardware configuration

Automatic encoding	Yes
<ul style="list-style-type: none"> • Mechanical coding element 	Yes
Selection of BaseUnit for connection variants	
<ul style="list-style-type: none"> • 1-wire connection 	BU type A0
<ul style="list-style-type: none"> • 2-wire connection 	BU type A0
<ul style="list-style-type: none"> • 3-wire connection 	BU type A0 with AUX terminals
<ul style="list-style-type: none"> • 4-wire connection 	BU type A0 + Potential isolation module

Digital inputs

Number of digital inputs	8
Digital inputs, parameterizable	Yes
Source/sink input	P-reading
Input characteristic curve in accordance with IEC 61131, type 2	Yes
Input voltage	
<ul style="list-style-type: none"> • Type of input voltage 	DC
<ul style="list-style-type: none"> • Rated value (DC) 	24 V
<ul style="list-style-type: none"> • for signal "0" 	-30 to +5V

• for signal "1"	+11 to +30V
Input current	
• for signal "1", typ.	6.8 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms (in each case + delay of 30 to 500 µs, depending on line length)
— at "0" to "1", min.	0.05 ms
— at "0" to "1", max.	20 ms
— at "1" to "0", min.	0.05 ms
— at "1" to "0", max.	20 ms
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
— permissible quiescent current (2-wire sensor), max.	2 mA
Isochronous mode	
Isochronous operation (application synchronized up to terminal)	No
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnostic messages	
• Diagnostic information readable	Yes
• Monitoring the supply voltage	Yes
— parameterizable	Yes
• Monitoring of encoder power supply	No
• Wire-break	No
• Short-circuit	No
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; Green LED
• for channel diagnostics	No
• for module diagnostics	Yes; green/red DIAG LED
Potential separation	
Potential separation channels	
• between the channels	No

- between the channels and backplane bus
- between the channels and the power supply of the electronics

Yes
No

Isolation

Isolation tested with 707 V DC (type test)

Ambient conditions

Ambient temperature during operation

- horizontal installation, min. 0 °C
- horizontal installation, max. 60 °C
- vertical installation, min. 0 °C
- vertical installation, max. 50 °C

Altitude during operation relating to sea level

- Ambient air temperature-barometric pressure-altitude On request: Ambient temperatures lower than 0 °C (without condensation) and/or installation altitudes greater than 2 000 m

Dimensions

Width	15 mm
Height	73 mm
Depth	58 mm

Weights

Weight, approx. 28 g

last modified: 10/15/2018