

1ft (30cm) Heavy Duty Power Cord, Twist-Lock NEMA L5-15P to NEMA 5-15R Black Adapter Cord, 15A 125V, 14AWG, Heavy Gauge Plug Converter Cable - UL Listed Components

**Product ID:** W31C-4100-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

## Certifications, Reports and Compatibility



## Applications

- Heavy Duty power cord supports high-powered equipment and PDUs
- Extend a server or rackmount equipment power cord by an additional 2ft

## Features

- **HEAVY DUTY ADAPTER CABLE:** 1ft (30cm) Adapter Power Cable with Twist-Lock NEMA L5-15P to NEMA 5-15R connector works with servers or high-power equipment; Locking L5-15 plug securely attaches to an outlet or power source; Indoor use; Rated up to 125V at 20A
- **BUILT FOR PERFORMANCE AND SAFETY:** Made with UL Listed components; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 1ft (30cm); TAA Compliant; Twist-Lock NEMA L5-15P to NEMA 5-15R; 14AWG; 125V 15A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.36in (9.3mm)
- **COMPATIBILITY:** NEMA L5-15P to NEMA 5-15R power cord works with North American PDUs and high-powered devices; Convert a NEMA L5-15 outlet to 5-15R for convenient integration with servers, switches, or UPS; Heavy duty adapter power cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, the heavy duty adapter power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This adapter power cable is available in other plug configurations

---

### Hardware

|                       |            |
|-----------------------|------------|
| Warranty              | Lifetime   |
| Number of Conductors  | 3          |
| Connector Plating     | Nickel     |
| Cable Jacket Material | PVC        |
| Fire Rating           | VW-1 Rated |
| Cable Type            | SJT        |

---

### Performance

|                      |                |
|----------------------|----------------|
| Maximum Cable Length | 1.0 ft [0.3 m] |
|----------------------|----------------|

---

### Connector(s)

|             |                                     |
|-------------|-------------------------------------|
| Connector A | 1 - NEMA L5-20P (North America)     |
| Connector B | 1 - NEMA 5-15 Power (North America) |

---

**Power**

|                |     |
|----------------|-----|
| Output Current | 15A |
|----------------|-----|

---

**Environmental**

|                       |                          |
|-----------------------|--------------------------|
| Operating Temperature | -20 to 105C (-4 to 221F) |
| Storage Temperature   | -20 to 105C (-4 to 221F) |
| Humidity              | 0% to 65% RH             |

---

**Physical Characteristics**

|                   |                   |
|-------------------|-------------------|
| Color             | Black             |
| Wire Gauge        | 14 AWG            |
| Cable Length      | 1.0 ft [0.3 m]    |
| Cable OD          | 0.4 in [9.3 mm]   |
| Product Length    | 12.0 in [30.5 cm] |
| Product Width     | 1.5 in [3.9 cm]   |
| Product Height    | 1.5 in [3.9 cm]   |
| Weight of Product | 0.0 oz [0.0 g]    |

---

**Packaging Information**

|                           |                   |
|---------------------------|-------------------|
| Package Length            | 5.7 in [14.5 cm]  |
| Package Width             | 11.5 in [29.3 cm] |
| Package Height            | 1.6 in [4.0 cm]   |
| Shipping (Package) Weight | 6.0 oz [170.0 g]  |

---

**What's in the Box**

|                     |   |
|---------------------|---|
| Included in Package | 1 - 1ft NEMA 5-15R to NEMA L5-15P Heavy-Duty Power Cord |
|---------------------|---|

---

*\*Product appearance and specifications are subject to change without notice.*