VISI-FLOAT® ACRYLIC FLOWMETERS 5" Scale, In-Line or Back Connection Options








VFC with 1" FNPT **End Connections**



VFC with 1" FNPT **Back Connections**





The Series VFC Visi-Float® Acrylic Flowmeters are direct reading, precision machined, clear acrylic body flowmeters suitable for both gas and liquid applications. This Series consists of two 5" (127 mm) scale flowmeters, the VFC and VFC II. The VFC features PVC 1" female NPT connections and the VFC II units are equipped with acetal thermoplastic 1" male NPT fittings.

FEATURES/BENEFITS

- · Bodies are cut and precision machined from solid, clear acrylic blocks allowing for complete visual inspection
- · White background allows for better visibility of the float increasing reading accuracy
- · Direct reading scales are hot stamped into the plastic eliminating the need for troublesome conversions and increasing product operating life
- · Precision machined tapered bore enables high repeatability
- · Low installation costs with back or end connection options

APPLICATIONS

- · Medical equipment
- · Laboratory equipment
- Air samplers
- · Gas analyzers
- · Pollution monitors
- · Chemical injectors
- · Cabinet purging
- Remediation
- · Osmosis skids

RANGE CHART - 5" SCALE - POPULAR RANGES				
Range No.	SCFM Air	Range No.	GPM Water	
121	4 to 25	141	.5 to 5	
122	5 to 50	142	1 to 10	
123	10 to 100	143	2 to 20	
Range No.	LPM Air	Range No.	LPM Water	
131	100 to 700	151	2 to 20	
132	200 to 1400	152	4 to 40	
133	300 to 2800	153	10 to 75	

SPECIFICATIONS

Service: Compatible gases & liquids.

Wetted Materials: Body: Acrylic plastic; O-ring: Buna-N (fluoroelastomer available); Metal parts: SS; Float: SS.

Fittings: VFC: PVC; VFCII: Acetal thermoplastic.

Temperature and Pressure Limits: 100 psig (6.9 bar) @ 120°F (48°C).

Accuracy: 2% of FS.

Process Connection: VFC: 1" female NPT back connections. End connections optional; VFCII: 1" male NPT back connections. End connections optional.

Scale Length: 5" typical length.

Mounting Orientation: Mount in vertical position.

Weight: 24 to 25 oz (.68 to .71 kg).

Agency Approvals: Meets the technical requirements of EU Directive 2011/65/EU

MODEL CHART			
Model	Thread Type	Process Connection	
VFC-X	1" FNPT	Back	
VFCII-X	1" MNPT	Back	
VFC-X-EC	1" FNPT	In-line end	
VFCII-X-EC	1" MNPT	In-line end	
How To Order: Series-Range NoOption			
Fxample: VEC-123-EC			

(Series VFC with 10-100 SCFM air range and 1" female NPT end connections)

OPTIONS			
To order add suffix:	Description		
-VIT	Fluoroelastomer O-rings		
-FDA	316 SS float & guide rod (only available		
	on VFCII with fluoroelastomer O-rings)		
-NIST	NIST traceable calibration certificate		
-BSPT	BSPT process connections		