

Cable Lacing

Features

- Designed for the lacing of cable forms
- Nylon core ensures high tensile strength
- Tolerant to most engine fluids
- Wide temperature range
- PVC sheath acts as a cushion preventing the cord from cutting into the cable insulation
- Includes a maximum limit on tensile strength to prevent excessive tension in lacing

RS PRO Cable Lacing Cord

RS Stock No: 265-8624



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Cable Lacing

Product Description

Use this high-quality lacing rope for professional cable management. This lacing cord is made from Nylon with a PVC coating which is strong enough for traditional lacing techniques such as square lashing and clove hitch. Our cord lacing is commonly used in telecommunication applications to create aesthetically pleasing or clean functional installations.

General Specifications

| | |
|----------|------------------------|
| Material | Nylon Core, PVC Coated |
| Colour | Black |
| Diameter | 0.71 mm |
| Length | 25 m |

Mechanical Specifications

| | |
|-----------------------------|--|
| Tensile Strength | 7.93Kg |
| Elongation Percentage | 5% |
| UV Resistance | Pass UL – 1581 720h Sunlight |
| Cold Flex Tolerance | -54°C UL – 1581 Cold Bend |
| Maximum Service Temperature | 138°C 168 Hours Continuous Exposure |
| Brittleness Temperature | -15°C A.S.T.M. D - 746 |
| Flame Resistance: Pass M | VSS 302, SAEJ369, & UL94 VO @ 125 mils |
| RoHS, Reach, ELV | Yes |