

6ft (1.8m) Power Extension Cord, IEC 60320 C14 to IEC 60320 C13 PDU Power Cord, 13A 250V, 16AWG, Black Extension Cable, AC Power Cable for PDU/Power Supply - UL Listed Components

**Product ID:** 8714-6600-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

## Certifications, Reports and Compatibility



## Applications

- Extend a monitor, scanner, printer, or PC power cord by an additional 6 ft

## Features

- **AC POWER CORD:** 6ft (1.83m) 16AWG power supply extension cable with IEC 60320 C14 to C13 connectors is suitable for workstations/home office or rack mounted equipment; Extend a C13 power cord to a power supply or PDU; Indoor use; Rated to carry 250V at 13A
- **BUILT FOR PERFORMANCE AND SAFETY:** Made with UL Listed components; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 6ft (1.83m); TAA Compliant; IEC 60320 C14 to IEC 60320 C13; 16AWG; 250V 13A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.33in (8.5mm)
- **COMPATIBILITY:** PC Power Cord IEC 60320 C14 works with North American PDUs and cables; IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more; Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to C13 power cord is available in other lengths

---

### Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

---

### Performance

Maximum Cable Length	6.0 ft [1.8 m]
----------------------	----------------

---

### Connector(s)

Connector A	1 - IEC 60320 C14 Power
-------------	-------------------------

Connector B 1 - IEC 60320 C13 Power

---

**Power**

Input Voltage 250 AC  
Input Current 13A

---

**Environmental**

Operating Temperature -20 to 105C (-4 to 221F)  
Storage Temperature -20 to 105C (-4 to 221F)  
Humidity 0% to 65% RH

---

**Physical Characteristics**

Color Black  
Wire Gauge 16 AWG  
Cable Length 6.0 ft [1.8 m]  
Cable OD 0.3 in [8.5 mm]  
Product Length 6.0 ft [1.8 m]  
Product Width 1.1 in [2.9 cm]  
Product Height 0.8 in [2.1 cm]  
Weight of Product 0.0 oz [0.0 g]

---

**Packaging Information**

Package Length 5.7 in [14.5 cm]  
Package Width 11.4 in [29.0 cm]  
Package Height 2.4 in [6.0 cm]  
Shipping (Package) Weight 10.6 oz [300.0 g]

---

**What's in the Box**

Included in Package 1 - 6ft C14 to C13 Power Cord

---

*\*Product appearance and specifications are subject to change without notice.*