



### Main

Range	Multi9
Product name	Multi9 PRD1
Product or Component Type	Surge arrester
Device short name	PRD1 75r
Poles description	4P
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network

### Complementary

Surge arrester class type	Type 1
Surge arrester technology	MOV
Wiring configuration	5-wire
Nominal discharge current	Common mode 20 kA L/PE) Common mode 20 kA N/PE) Differential mode 20 kA L/N)
Maximum discharge current	75 kA
[Iimp] impulse current	75 kA
[Uc] maximum continuous operating voltage	Common mode 175 V AC L/PE Common mode 175 V AC L/N Differential mode 350 V AC L/L Common mode 175 V AC N/PE
Maximum [Up] voltage protection level	Common mode <1200 V L/PE Common mode <600 V L/N Differential mode <1200 V L/L Common mode <600 V N/PE
Disconnecter device type	Associated circuit breaker 30 A C 10 kA
Short-circuit withstand	200 kA
Local signalling	Green mechanical indicator operating Red mechanical indicator end of life
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 mm pitches	8
Height	3.61 in (91.7 mm)
Width	2.76 in (70 mm)
Depth	2.81 in (71.4 mm)
Product Weight	24.80 oz (703 g)
Color	Gray RAL 7035)
Response Time	< 25 ns
Connections - terminals	Tunnel type terminal 0.01...0.05 in <sup>2</sup> (6...35 mm <sup>2</sup> ) AWG 10...AWG 2) - rigid Tunnel type terminal 0.01...0.04 in <sup>2</sup> (6...25 mm <sup>2</sup> ) AWG 10...AWG 4) - flexible Tunnel type terminal dry contacts) 0.00...0.00 in <sup>2</sup> (0.5...1.5 mm <sup>2</sup> )
Wire stripping length	0.39 in (10 mm) L/N 0.39 in (10 mm) PE 0.24 in (6 mm) dry contacts
Tightening torque	26.55 Lbf.in (3 N.m) L/N 26.55 lbf.in (3 N.m) PE

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Standards	UL 1449:ed. 4
IP degree of protection	Built-in NEMA 1
Pollution degree	3
Relative humidity	0...95 %
Operating altitude	6561.68 ft (2000 m)
Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)

## Ordering and shipping details

Category	08468-SURGE PROTECTION OEM
Discount Schedule	DE1B
GTIN	3606481585998
Returnability	Yes

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.15 in (8.0 cm)
Package 1 Width	3.54 in (9.0 cm)
Package 1 Length	4.72 in (12.0 cm)
Package 1 Weight	18.17 oz (515.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	12
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	14.37 lb(US) (6.52 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.