




REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	Redrawn in SW	11/26/2008	



Connection made via spring clamp.

To use: Placed stripped or ferruled wire into opening and press down on orange tab. This will lock the wire into place. Proceed to next terminal.



Acceptable wire AWG: 14 - 26AWG [2.5 - 0.14 sqmm]

MATERIALS	
HOUSING:	GLASS REINFORCED THERMOPLASTIC
SCREWS:	NICKEL PLATED BRASS HARDWARE
	NICKEL PLATED BRASS
RATINGS:	UL - 600V, 16A. EN 500V/6kV/3, 16A
APPROVALS:	UL & CSA

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF MENCOM CORPORATION. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF MENCOM CORPORATION IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED:		NAME	MENCOM CORPORATION	
DIMENSIONS ARE IN INCHES AND [MM]		DRAWN		DWM
		CHECKED		
		ENG APPR.		
		MFG APPR.		
		Q.A.		
		COMMENTS:		
MATERIAL			TITLE:	
FINISH			24 PL SQUICH MAL INSERT 25-48	
DO NOT SCALE DRAWING			SIZE DWG. NO. REV	
			B CSHM-24N A	
			SCALE: 1:1 WEIGHT: SHEET 1 OF 1	