

TP 6070-WVPS - Touch panel



1189629

<https://www.phoenixcontact.com/ca/products/1189629>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

IP66 Touch panel with 7-inch widescreen (16:9) VGA, PCAP display, Software: Visu+ RT



Your advantages

- PCAP touch interface, two-point multi touch control
- Fanless design
- Dual USB 2.0 ports
- Integrated Visu+ visualization software
- Ideal for use with PLCnext
- Configurable multifunction serial port

Commercial Data

Item number	1189629
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	D03
Product Key	DRCADC
GTIN	4063151236854
Weight per Piece (including packing)	2,084 g
Weight per Piece (excluding packing)	2,084 g
Customs tariff number	84714100
Country of origin	TW

TP 6070-WVPS - Touch panel



1189629

<https://www.phoenixcontact.com/ca/products/1189629>

Technical Data

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm® Cortex®-A9, 800 MHz
Operating system	Windows® Embedded Compact 7
Data storage	Flash eMMC, 8 GB
Slots	1x microSD

Display

Display type	17.8 cm/7" TFT
Screen resolution	800 x 480 Pixel(s) (WVGA)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	500 cd/m² typical (adjustable)
MTBF	50000 h
Color spectrum	16.7 million colors
Reading angle left	89 °
Reading angle right	89 °
Reading angle top	89 °
Reading angle bottom	89 °

Software

User software	Visu+
---------------	-------

System requirements

Runtime system	Visu+ Runtime
----------------	---------------

Interfaces

Interfaces	2x USB Host 2.0
	1x COM (RS-232/422/485)
Optional interfaces	Without optional interface
Network	1x Ethernet (10/100/1000 Mbps), RJ45
Bus system	without

Electrical properties

Supply

Supply voltage	24 V DC
Supply voltage range	18 V ... 32 V
Power supply unit	24 V DC ±20 %
Typical current consumption	0.61 A

Real-time clock

TP 6070-WVPS - Touch panel



1189629

<https://www.phoenixcontact.com/ca/products/1189629>

Realtime clock	Integrated (battery backup)
----------------	-----------------------------

Mounting

Mounting type	Front mounting
---------------	----------------

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Aluminum cast alloy, powder-coated

Connection data

Connection method	Screw connection
Conductor cross section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12
Conductor cross section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 2.5 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve	0.25 mm ² ... 2.5 mm ²
Stripping length	7 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66 (front), IP20 (back)
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 85 % (non-condensing)
Vibration (operation)	1g

Dimensions

External dimensions

Width / Height / Depth	202 mm / 146 mm / 51 mm (Dimensions of the front plate)
------------------------	---

Installation dimensions

Width / Height / Installation depth	195 mm / 139 mm / (Installation cutout)
-------------------------------------	---

TP 6070-WVPS - Touch panel



1189629

<https://www.phoenixcontact.com/ca/products/1189629>

Approvals



EAC

Approval ID: RU C-DE.A*08.B01708



IECEE CB Scheme

Approval ID: US-39088-UL



UL Listed

Approval ID: FILE E 238705



cUL Listed

Approval ID: FILE E 238705

TP 6070-WVPS - Touch panel



1189629

<https://www.phoenixcontact.com/ca/products/1189629>

Classifications

ECLASS

ECLASS-10.0.1	27330201
ECLASS-11.0	27330201
ECLASS-12.0	27330201
ECLASS-13.0	27330201

ETIM

ETIM 8.0	EC001412
----------	----------

UNSPSC

UNSPSC 21.0	43211900
-------------	----------

TP 6070-WVPS - Touch panel

1189629

<https://www.phoenixcontact.com/ca/products/1189629>



Environmental Product Compliance

REACH SVHC

Lead 7439-92-1

TP 6070-WVPS - Touch panel

1189629

<https://www.phoenixcontact.com/ca/products/1189629>



Accessories

TP6/WP6/VL3 MOUNTING HW (2PCS) - Panel-mount flange

1289537

<https://www.phoenixcontact.com/ca/products/1289537>



Mounting kit includes two retaining clips

TP/WP 6000 RTC BATTERY KIT - Battery

1289761

<https://www.phoenixcontact.com/ca/products/1289761>



Replacement battery for TP and WP 6000 touch panel

TP 6070-WVPS - Touch panel

1189629

<https://www.phoenixcontact.com/ca/products/1189629>



MICROSDHC-16GB - Memory

1154696

<https://www.phoenixcontact.com/ca/products/1154696>



Industrial grade 16 GB MicroSDHC 3DTLC

MICROSDHC-32GB - Memory

1154699

<https://www.phoenixcontact.com/ca/products/1154699>



Industrial grade 32 GB MicroSDHC 3DTLC

TP 6070-WVPS - Touch panel

1189629

<https://www.phoenixcontact.com/ca/products/1189629>



MSTB 2,5/ 3-STF-5,08 - PCB connector

1777992

<https://www.phoenixcontact.com/ca/products/1777992>



PCB connector, nominal cross section: 2.5 mm², color: green, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Tin, type of contact: Female connector, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: MSTB 2,5/...-STF, pitch: 5.08 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON MSTB 2,5, locking: Screw locking, mounting: Screw flange, type of packaging: packed in cardboard

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

8240 Parkhill Drive

Milton, Ontario L9T 5V7

1-800-890-2820

cdinfo@phoenixcontact.ca