



## Main

Range	Acti9
Range of product	Acti9 iEM3000
Device short name	iEM3455
Product or Component Type	Energy meter

## Complementary

Poles description	3P + N 1P + N 3P
Type of measurement	Active and reactive energy Active and reactive power Current Voltage
Metering type	Active, reactive, apparent energy (signed, four quadrant)
Device Application	Sub billing Multi-tariff Partial meter
Accuracy class	Class 0.5S active energy IEC 62053-22 Class 0.5S active energy ANSI C12.20
Input type	Split core current transducer 0.333 V or 1 V
Rated voltage	100...277 V +/- 20 % 173...480 V +/- 20 %
Network Frequency	60 Hz 50 Hz
Technology Type	Electronic
Display Type	LCD display
Sampling rate	32 samples/cycle
Measurement current	1...32767000 mA
Maximum value measured	99999999.9 kWh 99999999 MWh
Tariff input	Tariff 4)
Communication port protocol	Modbus RTU 9.6, 19.2 and 38.4 kbauds even/odd or none
Communication port support	Screw terminal block RS485
Local signalling	Green indicator light power ON Yellow flashing LED accuracy checking Alarm overload Yellow indicator light communications are active on the Modbus port (Modbus)
Number of inputs	1 digital 0...5 V/11...40 V 24 V DC
Number of Outputs	1 digital (static)
Output voltage	5...40 V DC@50 mA
Mounting Mode	Clip-on
Mounting Support	DIN rail

Connections - terminals	Current circuit screw terminals 0.01 in <sup>2</sup> (6 mm <sup>2</sup> ) Voltage circuit screw terminals 0.00 in <sup>2</sup> (2.5 mm <sup>2</sup> ) Input/Output circuit screw terminals 0.00 in <sup>2</sup> (1.5 mm <sup>2</sup> ) Communication screw terminals 0.00 in <sup>2</sup> (2.5 mm <sup>2</sup> )
Tightening torque	Input/Output circuit 4.43 lbf.in (0.5 N.m) Philips Voltage circuit 4.43 lbf.in (0.5 N.m) Philips Current circuit 7.08 lbf.in (0.8 N.m) pozidriv Communication 4.43 lbf.in (0.5 N.m) Philips
Wire stripping length	Input/Output circuit 0.24 in (6 mm) Voltage circuit 0.31 in (8 mm) Current circuit 0.31 in (8 mm) Communication 0.28 in (7 mm)
Standards	BS EN 61326-1 IEC 61326-1 EN 61326-1 BS EN 61010-1 EN 61010-1 IEC 61010-1 UL 61010-1 BS EN 61010-2-30 IEC 61010-2-30 EN 61010-2-30 UL 61010-2-30 ANSI C12.20
Product certifications	CE IEC 61010-1 safety) CE EN 61557-12 power monitor) CE EN/IEC 61326-1 EMC) UKCA BS EN 61010-1 safety) UKCA BS EN 61557-12 power monitor) UKCA BS EN 61326-1 EMC) CULus UL 61010-1 safety) CULus EN 61010-1 safety) KZ RCM

## Environment

IP degree of protection	Front panel IP40 IEC 60529 Body IP20 IEC 60529
IK degree of protection	IK08
Pollution degree	2
Relative humidity	5...95 % 97 °F (36 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C) - IEC
Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Operating altitude	< 9842.52 ft (3000 m)
Color	White
9 mm pitches	10
Width	3.54 in (90 mm)
Height	3.43 in (87 mm)
Depth	2.72 in (69 mm)

## Ordering and shipping details

Category	09786-SE ENTRY POWER METER
Discount Schedule	PL1
GTIN	3606480845222
Returnability	Yes
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.35 in (8.5 cm)
Package 1 Width	3.78 in (9.6 cm)
Package 1 Length	4.13 in (10.5 cm)
Package 1 Weight	11.89 oz (337 g)

Unit Type of Package 2	S03
Number of Units in Package 2	30
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	24.82 lb(US) (11.257 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	240
Package 3 Height	31.50 in (80 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	221.26 lb(US) (100.364 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.