

## FEATURES

- Mushroom emergency stop pushbutton in thermoplastic material
- 40mm diameter
- With latch, twist to release

## RS PRO Mushroom emergency stop pushbutton, with latch, twist to release, 2NC contacts

RS Stock No.: 2420837



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

# Emergency Stop Push Button

## Product Description

The E-STOP device SA series can be used for the emergency stop signal generation in dangerous situations. Equipped with certified emergency button, SA E-STOP devices guarantee maximum reliability and ease of installation. The SA series E-STOP devices can be used all over the world thanks to the compliance of ECX 4580 pushbutton with EN / IEC 60947-5-1, EN / IEC 60947-5-5 and EN ISO 13850 and UL NISD category.

## General Specifications

Casing Material	Thermoplastic
Operator	Emergency stop pushbutton ECX 4580 – Twist to release
Microswitch	2 NC
Connecting Terminals	Screw with captive cable clamp
Connecting Cables Dimensions [mm <sup>2</sup> ]	1 or 2 conductors - 0.5 ... 2.5

## Mechanical Specifications

Operating Temperatures [°C]	-40 / +70
Stock Temperatures [°C]	-40 / +70
Mechanical durability (Millions of operations)	0.3
B10d (million of operations)	0.6
Max. switching frequency [Cicli/h]	3600

## Electrical Specifications

Protection against electrical shocks	Class II - Double insulation
Rated Insulating Voltage $U_i$ [V]	690
Pollution Degree	3
Contact rating secondo UL508	A 600 Q 300
Rated impulsive voltage [kV]	8
Conventional thermal current in air free $I_{th}$ ( $\theta$ min 40 ° C) [A] ( $\theta$ )	10
Short circuit protection (EU min 500Vac - fuses type gG (g)) [A]	10
Rated Operational Current $I_e$ - AC-15 (50-60 Hz) [Vac - A]	24V - 10A / 240V - 6A / 400V - 4A
Rated Operational Current DC-13 [Vdc - A]	24V - 2,8A / 125V - 0.55A / 250V - 0.27A
Resistance Between Contacts [m $\Omega$ ]	25

# Emergency Stop Push Button



## Protection Category

IP Degree of Protection	65 (front panel) 20 (rear panel)
-------------------------	----------------------------------

## Additional Information

EAN	8000126233360
Custom Tariff Number	85371098

## Approvals

Declarations	CE – UKCA
Standards Met	IEC 60947-5-1 and IEC 60947-5-5