

The new EHP700LU 10,000 PSI batterypowered hydraulic pump sets a new benchmark for portability. During design and development, priority was given to performance, ergonomics and economic efficiency.

Choose between three job specific programs: crimping, cutting and punching.

The new Greenlee EHP700LU is suitable for operating single acting cutting, crimping and punching tools of up to 10,000 PSI.

CRIMPING

PUNCHING

CUTTING

MORE INTELLIGENT

- 3 in 1 program settings for crimping, cutting, and punching functions.
- Real-time crimp force monitoring with numeric digital display featuring IntelliCRIMP™ technology.
- Audible and visual fault alert.
- Real-time work history with downloadable PDF application.

ERGONOMIC

- The EHP700LU weighs a mere 14.1 pounds.
- Padded shoulder strap included for ease of transport.
- Operates in any orientation.
- On-board as well as corded remote activation switches.

POWER

- The EHP700LU operates from a single 18V battery with on-board storage for second battery.
- Pump provides real time charge status on both active and stored batteries.
- 18V lithium ion (Li-ion) battery provides 70% more cycles per charge.
- Available with 120V, 12V, or 230V battery charger.
- Available with 120V or 230V corded adapter for stationary applications.

CONNECTIONS

- Connections are UL and cUL classified for copper and aluminum, when used with Greenlee tools on 7 brands of color-coded lugs and splices.
- Most competitive tools are UL approved with only one connector brand.



Intelligent, versatile



and light weight, POWER ON THE GO!



CRIMPING - Setting #1 - Featuring Intelli-CRIMP[™] technology, Manual Retraction Stop (MRS), and Retraction Stop Repeat (MRS+).

- The new EHP700LU includes the Intelli-CRIMP™ System which monitors the entire crimping operation.
- Intelli-CRIMP™ Technology includes a pressure sensor that monitors the force of each crimp and provides the operator with an alert if the force is out of specification.
- Deviations to the maximum operation pressure of 10,000 PSI is noted by an audible signal and visual alert.
- The dashboard provides a visual tutorial on how to use the retraction interrupt features.

CUTTING - Setting #2

Automatic retraction reduces battery consumption and cycle times.

PUNCHING - Setting #3

The AutoSTOP feature of the EHP700LU monitors the pressure being applied to the ram. When the pressure drops after clearing the slug, the EHP700LU will automatically retract before the punch comes into contact with the die.

DIAGNOSTICS - Setting #7


- The diagnostic program shows work history of the pump as well as the charge level on the batteries.
 - The diagnostics setting tracks the following:
 - Total Time "t" = Total hours the pump has been in use.
 - Amperage Draw "Q" = Amp hours used during running time.
 - Full Pressure Cycles "n" = Number of full pressure cycles the unit has performed.
- The "Info Screen" provides the firmware number as well as the serial number for the pump.
- The "Bar <->PSI" Screen allows the user to switch the real time pressure monitoring from bar to PSI.



ORDERING INFORMATION

R = REPLACEMENT PART	A	= ACC
----------------------	---	-------

CAT NO.	UPC NO.	DESCRIPTION	STD PK		
EHP700LU11	00754	POWER PUMP, BAT 120V CHRGR	1		
EHP700LU12	00755	POWER PUMP, BAT 12V CHRGR			
EHP700LU22	00757	POWER PUMP, BAT 230V CHRGR			
EHP700LU120	00756	POWER PUMP, 120V ADAPTER	1		
EHP700LU230	00758	POWER PUMP, 230V ADAPTER	1		
01059	01059 🕢	HOSE ASSY, 1/4" X 6' 3/8M&3/8F FILLED	1		
01085	01085 🕢	HOSE ASSY, 1/4" X 6' 3/8M&1/4M FILLED	1		
05850	05850 🕢	HOSE ASSY, 1/4" X 10' 3/8M&3/8F FILLED	1		
17707	17707 🕢	HOSE ASSY, 1/4" X 10' 3/8M&1/4M FILLED	1		
25766	25766 🚯	ADAPTER, CHARGER 18V LI TO 12V NI	1		
52176	52176 🚯	BATTERY, 18V Li ION 3.0Ah	1		
52178	52178 🚯	CHARGER, BATTERY 120V	1		
52179	52179 🚯	CHARGER, BATTERY 230V	1		
52180	52180 🚯	CHARGER, BATTERY 12V	1		
EAC18120	52191 🚯	ADAPTER, AC - 120V TO 18V	1		
EAC18230	52192 🚯	ADAPTER, AC - 230V TO 18V	1		
EL122/32	02042 🚯	HYDRAULIC FLUID, BIODEGRADABLE			
HTA4GL	00759 🚯	REMOTE CONTROL	1		
TG3	01054 🚯	STRAP	1		
REMOTE HEADS					
RK06AT	06066	6T, QUAD POINT CRIMP TOOL, OPEN HEAD DIELESS	1		
RK06FT	06197	6T QUAD POINT CRIMP TOOL, FLIP TOP HEAD DIELESS	1		
RK1240	05351	12T CRIMP TOOL, 42MM			
RK1240C	07205	12T CRIMP TOOL, 42MM, PVC COVERED	1		
RK1550	05353	15T CRIMP TOOL, C-HEAD	1		
RK1550FT	00552	15T CRIMP TOOL, FLIP TOP HEAD	1		
RK6040	10604	CRIMPER, 60-TON	1		
SDK105	01870	REMOTE CABLE CUTTER - 4"	1		
746	17091	REMOTE KNOCKOUT RAM	1		
750	29149	CUTTER,CABLE HYD (750)	1		





CYCLES PER CHARGE EXAMPLES				
	Cycles	Material		
Crimping - 15 Ton remote	70	350 MCM		
Cutting - SDK105	76	750 MCM		
Punching - 2" with 746 Ram	150	14ga Steel		



SPECIFICATIONS				
Operating pressure:	10,000 PSI (700 bar)			
Oil volume:	0.80 qt (0.76l)			
Flow rate of double stage pump:				
Low pressure range:	up to 0.9 I/min			
At full pressure:	0.3 l/min			
Degree of protection:	IP43			
Battery voltage:	18 V			
Battery capacity:	3.0 Ah, Li-lon			
Number of batteries:	2 - 1 active, 1 stored			
Charging time:	30 minutes			
Ambient temperature:	10°F - 104°F (-12°C to 40°C)			
Weight:	10.8 lbs. (4.9 kg) without batteries			
Weight with 2 batteries:	14.1 lbs.			
Length:	14.0" (356mm)			
Width:	6.5" (165mm)			
Height:	11.5" (292mm)			

www.greenlee.com MA-5786 06/12