




KM label holder (standard holder)



Product information

Label holder for wire, cable and conduit labels. KM label holder accommodate BK identis and type KS as well as type KSO labels.

- Assembly with cable ties



Information, conformities and approvals



Article	Order No.	Color	Length mm (A)	Width mm (B)	Diameter min. mm (C)	Cable ties max. width mm	Recommended Labels	No. Idents BK23 / BK30	PU pcs.
Labelling across the cable/the conduit, single line of print									
KM 3	86321018	Transparent	16	4	5	5	KS 4/12 x	6 / 5	2000
Labelling lengthwise to the cable/the conduit, single line of print									
KM 4/12	86321015	Transparent	12	4	5	5	KS 4/x	5 / 3	2000
KM 4/18	86321019	Transparent	18	4	5	5	KS 4/x	7 / 6	2000
KM 4/23	86321020	Transparent	23	4	5	5	KS 4/x	10 / 7	1000
KM 4/31	86321024	Transparent	31	4	5	5	KS 4/x	13 / 10	1000
Labelling lengthwise to the cable/the conduit, one or more lines of print									
KM 9/20	86321040	Transparent	20	9	10	5	KSO 20x9		1000
KM 9/35	86321042	Transparent	35	9	10	5	KSO 35x9		500
KM 9/70	86321045	Transparent	70	9	10	5	KSO 70x9		250
KM 15/27	86321056	Transparent	27	15	14	5	KS 15/27		500
KM 15/49	86321058	Transparent	49	15	14	5	KS 15/49		250



KM label holder (standard holder)

Article	Order No.	Color	Length mm (A)	Width mm (B)	Diameter min. mm (C)	Cable ties max. width mm	Recommended Labels	No. Idents BK23 / BK30	PU pcs.
KM 15/67	86321060	Transparent	67	15	14	5	KS 15/67		125
Pre-assembled label holder, equipped with KB 55 cable ties									
KKM 4/12	86321048	Transparent	12	4	5	5	KS 4/x	5 / 4	250
KKM 4/23	86321050	Transparent	23	4	5	5	KS 4/x	10 / 7	250
KKM 9/20	86321052	Transparent	20	9	10	5	KS0 20x9		250
KKM 9/35	86321054	Transparent	35	9	10	5	KS0 35x9		250

Material properties



Polyvinyl chloride (PVC)

Thermal properties



Temperature / temperature range -40 °C – 60 °C

Fire properties



Fire classification V0

Assembly method



Cable tie system with sleeves

All details given in our sales brochures and catalogues, as well as the information available online, are based on our current knowledge of the products described. The electronic data and files made available by Murrplastik, particularly CAD files are based on our current knowledge of the product described. A legally binding assurance of certain properties or the suitability for a certain purpose can not be determined from this information. All information with respect to the chemical and physical properties of Murrplastik products, as well as application advice given verbally, in writing or by tests, is given to the best of our knowledge. They do not release the buyer from the obligation to carry out his own tests and trials in order to determine the concrete suitability of the products for the intended purpose. Murrplastik accepts no responsibility for the available information being up-to-date, correct or complete. Neither do we accept responsibility for the quality of this information. Murrplastik accepts no liability for damage caused as a result of using our products. Murrplastik reserves the right to make technical changes and improvements through constant further development of products and services. Our General Terms and Conditions apply.