


## **Features**

- High pressure capability
- Sensorless, brushless external controller
- Self-priming
- High and low viscosity fluids
- Reversable flow
- High chemical resistance
- Small size
- No dynamic seal

## **RS PRO Water Pump**

RS Stock No.: 125-3560



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## **Water Pump**



#### **Product Description**

The MGD1000 series micropump, delivers consistent almost pulseless flow with high or low pressure. They are suitable for a wide range of liquids and are self-priming. The MGD1000 can be used with all common liquids and will also resist most chemicals and solvents. Its flow direction is reversible. The MGD1000 range has 3 different gear variations for different uses. (P) for highest pressure performance, (F) for highest flow performance and (S) for a balance between the two.

These pumps are particularly suitable for systems where pressure and flow consistency are key requirements. Typical applications include Dosing, Medical devices, Fuel cells, High pressure fuel pump, Cooling systems, Precision flow, Lubrication.

The MGD1000 requires a controller to run, included in this package is the EQI-MG1 designed specifically for this pump. The EQI-MG1 offers speed and flow control via onboard potentiometer or external 0-4v analogue control with a wide 6-28v input voltage range in which the driver will monitor and govern speed accordingly. You can also reverse the flow direction.

#### **General Specifications**

Туре	Micro External Gear Pump		
Maximum Flow Rate	550ml/min		
Input Connection	1/8 BSP threads fitted with 6mm ID push fit connectors		
Input Connection Size	6.0mm O.D Tubing		
Output Connection Size	6.0mm O.D Tubing		
Maximum Pressure	8 BAR (RECOMMENDED)		
Maximum System Pressure	25 BAR		
Wetted materials	316 Stainless Steel, PEEK, PET, Nickel, FKM		
Coupling Type	Direct drive, seal-less		
Maximum Fluid Temperature	80°C		
Head Type	Single		
Noise Level	<60db (Measured 1 metre from pump)		
Auto On/Off Switch	No		
Built-in Water Filter	No		

#### **Electrical Specifications**

Connection	Requires controller (DC input)	
Supply Voltage	6-28v	
Input Power	6-28W (0-8 BAR @ 12V)	



### **Mechanical Specifications**

Dimensions	30 x 32 x 75 mm
Weight	130g

### **Protection Category**

Safety Category Level	S1
IP Rating	IP 45
Insulation class	A

#### **Approvals**

Compliance/Certifications	ISO 9001 Quality Control Standard
Declarations	TCS Declaration of Conformity - RoHS Directive 2011/65/EU, SVCH, CMRT,
	3TG and REACH compliant.

#### **Similar Products**

Stock No.	Brand	Maximum Flow Rate	Input Connection	Input Power
125-3561	RS PRO	1100ml/min	DC	35W
125-3562	RS PRO	400ml/min	DC	28W
125-3568	RS PRO	-	DC	-
817-0722	RS PRO	550ml/min	DC	28W
817-0734	RS PRO	400ml/min	DC	28W

# **Water Pump**



TEST CONDUCTED ON 10:1 WATER GLYCOL MIXTURE AT 12V USING AN EQI-MG1 CONTROLLER. PUMP HAS BEEN CONTROLLED AND OPERATED VIA 0-4V ANALOGUE INPUT

