

STW-6500WA Basic Terminal



Features:

- Aluminum Front Panel
- 16 Million Colors
- · Enhanced Cybersecurity
- Easy to Install, No Tools Needed
- Single Touch Analog Display
- 2 Ethernet Ports


Lilianced Cybersecui		• 2 Ethernet Ports	
Perfor	mance Sp	ecifications	
Model		STW6500WA	
Graphics Display Resolution		WSVGA TFT(1,024 x 600 Pixels)	
Display Type and Size		TFT Color LCD (10.1-inch) Wide	
Display Colors		16 million colors	
Touch Panel		Resistive film (analog, single touch)	
Effective Display Area		222.72 x 125.28 mm (8.77 x 4.93 in)	
ToucPanel Resolution		1024 x 1024	
Backlight		Backlight White LED (Not user replaceable. When replacement is required, contact customer support.)	
Backlight Service Life		50,000 hours or more (continuous operation at 25 °C [77 °F] before backlight brightness decreases to 25%)	
Brightness Control		16 levels (Adjusted with touch panel or software)	
Interface	USB (Type A)	Connector: USB 2.0 (Type A) x 1, Power supply voltage: 5 Vdc ±5 %, Maximum current supplied: 500 mA, Communication distance: 5 m [16.4 ft.]	
	USB (Type - microB)	The USB (micro-B) interface is disabled.	
	Ethernet	IEEE802.3i/IEEE802.3u, 10BASE-T/100BASE-TX, Connector: Modular jack (RJ-45) x 2 *1	
1 ETH1 and E	TH2 have the same IF	P address and MAC address.	

General Specification	ns	
Model	STW6500WA	
Input Voltage	Rated Input Voltage: 24 Vdc / Input Voltage Limits: 19.2 to 28.8 Vdc	
Power Consumption	9.6 W or less when power is not supplied to devices via fron USB, 4.6 W or less when screen turns off the backlight (standby mode) (Max 12.6 W)	
In-Rush Current	30 A or less	
Storage Temperature	-20 to 60 °C (-4 to 140 °F)	
Shock Resistance	IEC/EN 61131-2 compliant 147 m/s2, X, Y, Z directions for 3 times	
Certifications	UL 61010-2-201 and CSA C22.2 No61010-2-201, KC KN1, KN61000-6-2, RCM EN61000-6-4, CE EN 61131-2, EN61000-6-4, EN61000-6-2, ROHS, REACH Regulation EC 1907/2006, WEEE Directive 2012/19/EU	
Operating Temperature	0 to 50 °C (32 to 122 °F)	
Voltage Drop	10 ms or less	
Corrosive Gas	Free of corrosive gases	
Pollution Degree	For use in pollution degree 2 environment	
Cooling method	Natural air circulation	
Dust	0.1 mg/m3 (10-7 oz/ft3) or less (non-conductive levels)	
Voltage Endurance	1,000 Vac, 20 mA for 1 minute (between charging and FG terminals)	
Vibration Resistance	IEC/EN 61131-2 compliant, 5 to 9 Hz single amplitude 3.5 mm [0.14 in.], 9 to 150 Hz fixed acceleration: 9.8 m/s2, X, Y, Z directions for 10 cycles (approx. 100 min.)	
Insulation Resistance	500 Vdc, 10 MΩ or more	
Structure	IP65F, Type 1, Type 4X (indoor use only), Type 13 (on the front panel when properly installed in an enclosure) *2	
Weight	1.3 kg (2.87 lb) or less	
External Dimensions	273 x 203 x 47 mm (10.75 x 7.99 x 1.85 in)	
Panel Cut-Out Dimensions	255 x 185 mm (10.04 x 7.28 in)*2 Panel thickness area: 1.65 mm (0.060.2 in)*3	
Warranty	Two (2) years	

² For dimensional tolerance, everything +1/-0 mm (+0.04/-0 in) and R in angle are below R3 (R0.12 in)

³ Even if the installation wall thickness is within the recommended range for the "Panel Cut Dimensions", depending on wall's material, size, and installation location of this product and other





Ordering Information				
Model Number	Description			
PFXSTW6500WAD	10.1"W Basic Web Terminal 10.1"W 1024 x 600 pixel 16M colors display with analog signal touch panel, Ethernet(RJ45) x 2, USB Host, 24VDC, nonexpandable			

mm in.	A	R5 R0.20	
Panel Cut Out	А	В	С
1 anei out out			

Options					
Part Number	Description				
PFXZCIAFTF1	Installation fastener (2 pieces/set).				
PFXZCIWG103	Installation Gasket				
CA5-DCCNM-01	Connector to connect DC power supply cables.				
PFXZCIDS102	Disposable, dirt-resistant sheet for the display (5 sheets/set) for STW-6500WA.				
FP-US00	Connects a USB device.				
CA5-USBEXT-01	Extension cable that attaches USB interface to front panel.				
PFXZCBCLUSA1	Clamp to prevent disconnection of USB cable (USB Type A, 1 port, 5 clamps/set)				

Pro-face America

Phone: 734.477.0600 www.profaceamerica.com Customer Service Hotline: 800.289.9266



www.profaceamerica.com