N-M CLAMP RG8, RG9, RG11

SC9173

₽

SPECIFICATIONS ELECTRICAL:		0.78"	
FREQUENCY: 0-12 GHZ VSWR 1.3:1 MAX IMPEDANCE: 50 OHMS	Ø.68"		
MECHANICAL:		.250"->	
MATERIAL BODY: NICKLE PLATED BRASSS CENTER CONTACT: BRASS CONTACT PLATING: Si QQ-S-365 INSULATOR: TEFLON INTERFACE: MIL-STD-348B ROHS COMPLIANT			⇒
OP. TEMP RANGE: -55°C- +155°C			
ASSEMBLY INSTRUCTIONS: TRIM CABLE TO OVERALL LENGTH AS SHOWN; SLIDE BACKNUT, WASHER, GASKET, CLAMP ON CABLE; COMB BRAID WIRES OUT, FOLD BACK, TRIM FLUSH W CLAMP; TRIM DIELECTRIC & CENTER PIN AS SHOWN; ASSEMBLE REAR BUSHING; SOLDER CONTACT ONTO CENTER CONDUCTOR, INSERT ASSEMBLY INTO BODY, TIGHTEN NUT	STRIPPING DIMENSIONS		
	FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		
	N-M CLAMP RG8, RG9, RG11		
		DDE DWG NO	
	A 3FKR	5 3C9173	
	<u></u>		

 \forall