

Product data sheet

Characteristics

EIK1

Interlock, safety switch, 1 x NO, 1 x NC contact, general duty series F 100A to 200A rated or heavy duty series F5/F6/F7



Main

| | |
|---------------------------|---------------|
| Product or Component Type | Interlock |
| Product destination | Safety switch |

Complementary

| | |
|------------------------|----------------------|
| Product Certifications | UL Listed |
| Switch Function | SPDT |
| Height | 4.343 in (110.31 mm) |
| Width | 7.263 in (184.48 mm) |
| Depth | 1.48 in (37.59 mm) |

Ordering and shipping details

| | |
|-------------------|-------------------------------|
| Category | 00058-MISC SWITCH ACCESSORIES |
| Discount Schedule | DE1 |
| GTIN | 785901751304 |
| Returnability | Yes |
| Country of origin | US |

Packing Units

| | |
|------------------------------|---------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.90 in (9.906 cm) |
| Package 1 Width | 6.20 in (15.748 cm) |
| Package 1 Length | 7.00 in (17.78 cm) |
| Package 1 Weight | 11.20 oz (317.515 g) |
| Unit Type of Package 2 | PAL |
| Number of Units in Package 2 | 210 |
| Package 2 Height | 27.50 in (69.85 cm) |
| Package 2 Width | 40.00 in (101.6 cm) |
| Package 2 Length | 48.00 in (121.92 cm) |
| Package 2 Weight | 172.00 lb(US) (78.018 kg) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|