



Main

Range	PowerLogic
Product name	PowerLogic PM5000
Device short name	PM5330
Product or Component Type	Power meter

Complementary

Power quality analysis	Up to the 31st harmonic
Device Application	Power monitoring Multi-tariff
Type of measurement	Current Voltage Frequency Power factor Energy Active and reactive power
Supply voltage	90...450 V AC 45...65 Hz 100...300 V DC
Network Frequency	50 Hz 60 Hz
Line Rated Current	1 A 5 A
Type of network	3P + N 3P 1P + N
Maximum power consumption in VA	11 VA 415 V
Ride-through time	80 Ms 120 V AC typical 100 Ms 230 V AC typical 100 Ms 415 V AC typical 50 ms 125 V DC typical
Display Type	Monochrome graphic LCD
Display Resolution	128 x 128 pixels
Sampling rate	64 samples/cycle
Measurement current	5...8500 mA
Analogue input type	Voltage 5 MOhm) Current <= 0.3 mOhm)
Measurement voltage	35...760 V AC 45...65 Hz between phases 20...400 V AC 45...65 Hz between phase and neutral
Frequency measurement range	45...65 Hz
Number of inputs	2 digital

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Measurement accuracy	Active energy +/- 0.5 % Reactive energy +/- 2 % Active power +/- 0.5 % Apparent power +/- 0.5 % Frequency +/- 0.05 % Power factor +/- 0.5 Current +/- 0.5 % Voltage +/- 0.5 % Apparent energy +/- 0.5 % Reactive power +/- 2 %
Accuracy class	Class 0.5S active energy IEC 62053-22
Number of Outputs	2 relay 2 digital
Information displayed	Tariff 4)
Communication port protocol	Modbus RTU and ASCII 9.6, 19.2 and 38.4 kbauds even/odd or none - 2 wires 2500 V JBUS
Communication port support	RS485
Data recording	Maintenance logs Time stamping Alarm logs Data logs Min/Max of instantaneous values Event logs
Memory capacity	256 kB
Connections - terminals	Voltage circuit screw terminal block4 Control circuit screw terminal block2 Current transformer screw terminal block6 Input/Output circuit screw terminal block6 Relay output screw terminal block4 Ethernet network RJ45 connector
Mounting Mode	Flush-mounted
Mounting support	Framework
Standards	UL 61010-1 IEC 62053-22 IEC 61557-12 EN 50470-3 IEC 60529 IEC 62053-24 EN 50470-1
Product certifications	CE IEC 61010-1 CULus UL 61010-1
Width	3.78 in (96 mm)
Depth	2.83 in (72 mm)
Height	3.78 in (96 mm)
Product Weight	15.17 oz (430 g)

Environment

Electromagnetic compatibility	Conducted and radiated emissionsclass B EN 55022 Immunity to conducted disturbances 150 kHz...80 MHzlevel 4 IEC 61000-4-6 Electrical fast transient/burst immunity testlevel 3 IEC 61000-4-4 Radiated radio-frequency electromagnetic field immunity testlevel 4 IEC 61000-4-3 Voltage dips and interruptions immunity testclass B IEC 61000-4-11 Limits for harmonic current emissionsclass A IEC 61000-3-2 Electrostatic dischargelevel 4 IEC 61000-4-2 Conducted RF disturbanceslevel 3 IEC 61000-4-6 Magnetic field at power frequencylevel 4 IEC 61000-4-8 Immunity to conducted disturbances 150 kHz...80 MHz IEC 61000-4-6 Electrical fast transient/burst immunity test IEC 61000-4-4 Radiated radio-frequency electromagnetic field immunity test IEC 61000-4-3 Voltage dips and interruptions immunity test IEC 61000-4-11 Limitation of voltage changes, voltage fluctuations and flicker in low-voltage IEC 61000-3-3 Electrostatic discharge 8 kVlevel 4 IEC 61000-4-2
IP degree of protection	Display IP54 IEC 60529 Rear IP30 IEC 60529
Relative humidity	5...95 % 122 °F (50 °C) non-condensing
Pollution degree	2
Ambient air temperature for operation	-13...158 °F (-25...70 °C) meter

Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
Operating altitude	6561.68 ft (2000 m) CAT III 9842.52 ft (3000 m) CAT II

Ordering and shipping details

Category	09777-POWERLOGIC PM5000 HARDWARE
Discount Schedule	PL1
GTIN	3606480614026
Returnability	Yes
Country of origin	IN

Packing Units


Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.33 in (11.0 cm)
Package 1 Width	4.96 in (12.6 cm)
Package 1 Length	4.96 in (12.6 cm)
Package 1 Weight	19.40 oz (550.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	16.76 lb(US) (7.6 kg)
Unit Type of Package 3	P12
Number of Units in Package 3	288
Package 3 Height	41.34 in (105.0 cm)
Package 3 Width	31.50 in (80.0 cm)
Package 3 Length	47.24 in (120.0 cm)
Package 3 Weight	455.03 lb(US) (206.4 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Approximate Dimensions

PM5000 Series Meters



PM5000 Series Remote Display

